




LOC	DIST	REVISIONS				
		REV	DATE	BY	APP'D	REASON
DF	DO	R	27-May-15	MGM	CT	REVISED PER ECO-15-005918

1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308.
2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA.
3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS.
4. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M39029/63-368 OR ANY TYCO HD-20 SOCKET CONTACT. CONTACTS ORDERED SEPARATELY.
5. TYCO PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS.
6. UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.
7. RESTRICTED ITAR DRAWING.
8. FINISH: CADMIUM PER QQ-P-416.
9. FINISH: BRIGHT TIN PER ASTM-B-545 .000400-.000550 THK OVER COPPER PER AMS2418 .000050 MIN THK.



	-	9	STEEL PER ASTM-A-109	-	205167-5	205167-5
	-	7	-	-	-	205167-4
SUPSD BY 205291-1	-	8	STEEL PER ASTM-A-109	-	205167-3	205167-3
SUPSD BY 206803-2	-	-	BRASS	M24308/6-4F	205561-4	205167-2
M24308/2-284F	5	8	STEEL PER ASTM-A-109	M24308/2-4F	205561-2	205167-1
MILITARY P/N ON PACKAGE	REMARKS	SHELL FINISH	SHELL MAT'L	MARKED MILITARY PART NO.	MARKED TYCO PART NO.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MANJUNATH G M 27-May-15	TE Connectivity	
DIMENSIONS: INCHES		CHK CHARLES THOMAS 31-JAN-03	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHARLES THOMAS	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		
1 PLC ± -		SIZE		
2 PLC ± -		CAGE CODE		
3 PLC ± .005		DRAWING NO		
4 PLC ± -		RESTRICTED TO		
ANGLES ± - 0°30'		WEIGHT		
MATERIAL SEE CALLOUTS		A1 00779 205167		
SEE CALLOUTS		CUSTOMER DRAWING		
		SCALE 4:1 SHEET 1 OF 1 REV R		