

SCOPE: CMOS, BUFFERED, MULTIPLYING 8-BIT D/A CONVERTER

<u>Device Type</u>	<u>Generic Number</u>	<u>Circuit Function</u>
01	MX7524S(x)/883B	DAC with .5 LSB
02	MX7524T(x)/883B	DAC with .25 LSB
03	MX7524U(x)/883B	DAC with .125 LSB

Case Outline(s). The case outlines shall be designated in Mil-Std-1835 and as follows:

<u>Outline Letter</u>	<u>Mil-Std-1835</u>	<u>Case Outline</u>	<u>Package Code</u>
MAXIM SMD			
Q E	GDIP1-T16 or CDIP2-T16	16 LEAD Cerdip	J16
E 2	CQCC1-N20	20 LCC	L20

Absolute Maximum Ratings:

V_{DD} to GND	-.3V, +17V
V_{RFB} to GND	$\pm 25V$
V_{REF} to GND	$\pm 25V$
Digital Input Voltage to GND	-0.3V to V_{DD}
V_{OUT1} , V_{OUT2} , 0 to GND	-0.3V to V_{DD}

Lead Temperature (soldering, 10 seconds) +300°C

Storage Temperature -65°C to +150°C

Continuous Power Dissipation $T_A = +70^\circ C$

16 pin Cerdip (derate 10mW/°C above +70°C) 800mW

20 pin LCC (derate 9.1mW/°C above +70°C) 727mW

Junction Temperature T_J +150°C

Thermal Resistance, Junction to Case, θ_{JC}

16 pin Cerdip 50°C/W

20 pin LCC 20°C/W

Thermal Resistance, Junction to Ambient, θ_{JA} :

16 pin Cerdip 100°C/W

20 pin LCC 110°C/W

Recommended Operating Conditions

Ambient Operating Range (T_A) -55°C to +125°C

Supply Voltage Range (V_{DD}) +5V to +15V

Stresses beyond those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TABLE 1. ELECTRICAL TESTS:

TEST	Symbol	CONDITIONS -55 °C ≤ T _A ≤ +125 °C 1/ Unless otherwise specified	Group A Subgroup	Device type	Limits Min	Limits Max	Units
ACCURACY							
Resolution	RES	V _{DD} =+5V and V _{DD} =+15V	1,2,3	All	8.0		Bits
Relative Accuracy	RA	V _{DD} =+5V	1,2,3	All		±0.5	LSB
Relative Accuracy	RA	V _{DD} =+15V	1,2,3	01		±0.5	LSB
			1 2,3	02		±0.5 ±0.25	
		V _{DD} =+15V, T _A =25°C, NOTE 2	12	02 03		±0.25 ±0.125	
			1 2,3	03		±0.5 ±0.125	
Gain Error NOTE 3	AE	V _{DD} =+5V	1 2,3	All		±1.0 ±1.4	%/FSR
Gain Error NOTE 3	AE	V _{DD} =+15V	1 2,3	All		±0.5 ±0.6	%/FSR
Power Supply Rejection	PSRR	V _{DD} =+5V, ΔV _{DD} =±10%	1 2,3	All		±0.08 ±0.16	%/%
Power Supply Rejection	PSRR	V _{DD} =+15V, ΔV _{DD} =±10%	1 2,3	All		±0.02 ±0.04	%/%
Output Leakage Current	I _{OUT1}	V _{DD} =+5V DB0-DB7=0V, WR=CS=0V	1 2,3	All		±50 ±400	nA
Output Leakage Current	I _{OUT1}	V _{DD} =+15V DB0-DB7=0V, WR=CS=0V	1 2,3	All		±50 ±200	nA
Output Leakage Current	I _{OUT2}	V _{DD} =+5V DB0-DB7=V _{DD} , WR=CS=0V	1 2,3	All		±50 ±400	nA
Output Leakage Current	I _{OUT2}	V _{DD} =+15V DB0-DB7=V _{DD} , WR=CS=0V	1 2,3	All		±50 ±200	nA
Input Resistance	R _{IN}	V _{DD} =+5V and +15V	1,2,3	All	5	20	kΩ
Digital Input High Voltage	V _{IH}	V _{DD} =+5V V _{DD} =+15V	1,2,3	All	2.4 13.5		V
Digital Input Low Voltage	V _{IL}	V _{DD} =+5V V _{DD} =+15V	1,2,3	All		0.8 1.5	V
Digital Input Leakage Current	I _{IN}	V _{DD} =+5V V _{IN} =0V or V _{DD}	1,2,3	All		±1.0 ±10	μA
Digital Input Leakage Current	I _{IN}	V _{DD} =+15V V _{IN} =0V or V _{DD}	1,2,3	All		±1.0 ±10	μA
Supply Current	I _{DD}	V _{DD} =+5V V _{DD} =+15V	1,2,3	All		2.0 2.0	mA
		All digital inputs V _{IL} or V _{IH}					
Supply Current	I _{DD}	V _{DD} =+5V V _{DD} =+15V	1,2,3	All		100 500	μA
		All digital inputs 0V or V _{DD}					
Gain Temperature Coefficient NOTE 3	TC _{AE}	V _{DD} =+5V V _{DD} =+15V	1,2,3	All		±40 ±10	ppm/°C

TEST	Symbol	CONDITIONS -55 °C ≤ T _A ≤ +125°C 1/ Unless otherwise specified	Group A Subgroup	Device type	Limits Min	Limits Max	Units
Feedthrough Error NOTE 4, NOTE 5	FT	V _{DD} =+5V or V _{DD} =+15V, V _{REF} =+10V, 100kHz sinewave, DB0-DB7=0V, $\overline{WR}=\overline{CS}=0V$	4,5,6	All		50	mVp-p
Digital Input Capacitance NOTE 6	C _{IN}	V _{DD} =+5V V _{IN} =0V, DB0-DB7	4	All		5	pF
Digital Input Capacitance NOTE 6	C _{IN}	V _{DD} =+15V V _{IN} =0V, $\overline{WR}$, $\overline{CS}$	4	All		20	pF
Digital Input Capacitance NOTE 6	C _{IN}	V _{DD} =+5V V _{IN} =0V, $\overline{WR}$, $\overline{CS}$	4	All		5	pF
Digital Input Capacitance NOTE 6	C _{IN}	V _{DD} =+15V				20	pF
ANALOG INPUTS							
Digital Output Capacitance NOTE 6	C _{OUT1}	V _{DD} =+5V and 15V, $\overline{DB0-DB7}=V_{DD}$, $\overline{WR}=\overline{CS}=0V$	4	All		120	pF
Digital Output Capacitance NOTE 6	C _{OUT2}					30	
Digital Output Capacitance NOTE 6	C _{OUT1}	V _{DD} =+5V and 15V, $\overline{DB0-DB7}=0V$, $\overline{WR}=\overline{CS}=0V$	4	All		30	pF
Digital Output Capacitance NOTE 6	C _{OUT2}					120	
TIMING							
Chip select to write setup time NOTE 7	t _{CS}	V _{DD} =+5V	9,10,11	All	240		ns
Chip select to write hold time NOTE 7	t _{CH}	V _{DD} =+15V			150		
Chip select to write hold time NOTE 7	t _{CH}	V _{DD} =+5V	9,10,11	All	0		ns
Chip select to write hold time NOTE 7	t _{CH}	V _{DD} =+15V					
Write pulse width NOTE 7	t _{WR}	V _{DD} =+5V, t _{CS} ≥ t _{WR} , t _{CH} ≥ 0	9,10,11	All	240		ns
Write pulse width NOTE 7	t _{WR}	V _{DD} =+15V, t _{CS} ≥ t _{WR} , t _{CH} ≥ 0			150		
Data setup time NOTE 7	t _{DS}	V _{DD} =+5V	9,10,11	All	170		ns
Data setup time NOTE 7	t _{DS}	V _{DD} =+15V			100		
Data hold time NOTE 7	t _{DH}	V _{DD} =+5V	9,10,11	All	10		ns
Data hold time NOTE 7	t _{DH}	V _{DD} =+15V			10		
Output Current Settling Time NOTE 4, 8	t _{SL}	V _{DD} =+5V	9,10,11	All		500	ns
Output Current Settling Time NOTE 4, 8	t _{SL}	V _{DD} =+15V				350	

NOTE 1: V_{OUT1}=V_{OUT2}=0V; V_{REF}=+10V, unless otherwise specified.

NOTE 2: Optional Subgroup 12 is used for grading and part selection at +25°C.

NOTE 3: Measured using internal feedback RFB and includes effect of leakage current and gain TC.

NOTE 4: Guaranteed, if not tested.

NOTE 5: Feedthrough error can be reduced by connecting the metal lid to ground.

NOTE 6: Subgroup 4 (C_{IN} and C_{OUT} measurements) shall be measured only for the initial test and after process or design changes which may affect capacitance.

NOTE 7: Timing in accordance with Write Cycle Timing Diagram in Commercial Datasheet. $\overline{DB0-DB7}$

NOTE 8: ROUT1 load=100Ω, CEXT=13pF. DB0-DB7=0V to V_{DD} or V_{DD} to 0V, WR, CS=0V.
Extrapolated: tS(±1/2LSB)=tpD+6.2T, where T=the measured first time constant of the final RC delay.

MODE SELECTION TABLE:

$\overline{\text{CS}}$	$\overline{\text{WR}}$	MODE	DAC Response
L	L	Write	DAC responds to data bus (DB0-DB7) inputs
H	X	Hold	Data bus (DB0-DB7) is locked out; DAC holds last data present when $\overline{\text{WR}}$ or $\overline{\text{CS}}$ assumed HIGH state
X	H	Hold	

L = Low state, H = High state, X = Don't care

ORDERING INFORMATION:

	Package	Pkg. Code	Maxim Part Number	SMD Number
01	16 pin CERDIP	J16	MX7524SQ/883B	5962-8770001EA
01	20 pin LCC	L20	MX7524SE/883B	5962-87700012C
02	16 pin CERDIP	J16	MX7524TQ/883B	5962-8770002EA
02	20 pin LCC	L20	MX7524TE/883B	5962-87700022C
03	16 pin CERDIP	J16	MX7524UQ/883B	5962-8770003EA
03	20 pin LCC	L20	MX7524UE/883B	5962-87700032C

TERMINAL CONNECTIONS:

	J16	L20
Pin		
1	OUT1	NC
2	OUT2	OUT1
3	GND	OUT2
4	DB7(MSB)	GND
5	DB6	DB7(MSB)
6	DB5	NC
7	DB4	DB6
8	DB3	DB5
9	DB2	DB4
10	DB1	DB3
11	DB0(LSB)	NC
12	$\overline{\text{CS}}$	DB2
13	$\overline{\text{WR}}$	DB1
14	V _{DD}	DB0(LSB)
15	VREF	$\overline{\text{CS}}$
16	RFB	NC
17		$\overline{\text{WR}}$
18		V _{DD}
19		VREF
20		RFB

QUALITY ASSURANCE

Sampling and inspection procedures shall be in accordance with MIL-Prf-38535, Appendix A as specified in Mil-Std-883.

Screening shall be in accordance with Method 5004 of Mil-Std-883. Burn-in test Method 1015:

1. Test Condition, A, B, C, or D.
2. TA = +125°C minimum.
3. Interim and final electrical test requirements shall be specified in Table 2.

Quality conformance inspection shall be in accordance with Method 5005 of Mil-Std-883, including Groups A, B, C, and D inspection.

Group A inspection:

1. Tests as specified in Table 2.
2. Selected subgroups in Table 1, Method 5005 of Mil-Std-883 shall be omitted.

Group C and D inspections:

- a. End-point electrical parameters shall be specified in Table 1.
- b. Steady-state life test, Method 1005 of Mil-Std-883:
 1. Test condition A, B, C, D.
 2. TA = +125°C, minimum.
 3. Test duration, 1000 hours, except as permitted by Method 1005 of Mil-Std-883.

TABLE 2. ELECTRICAL TEST REQUIREMENTS

Mil-Std-883 Test Requirements	Subgroups per Method 5005, Table 1
Interim Electric Parameters Method 5004	1
Final Electrical Parameters Method 5005	1*, 2, 3
Group A Test Requirements Method 5005	1, 2, 3, 4, 5, 6, 9, 10**, 11**, 12
Group C and D End-Point Electrical Parameters Method 5005	1

* PDA applies to Subgroup 1 only.

** Subgroups 10 and 11, if not tested shall be guaranteed to the limits specified in Table 1.