

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
				D		REV PER ECR 09-025898	02DEC09	JR	TM

INSULATION

SLEEVE

BODY

1

5.26±0.08
[.207±.003]
FOR M5 STUD

9.78
[.385]

4.95 [.195]

7.92
[.312] MIN

18.19 [.716] MAX

23.40 [.921] MAX

6

1 STAMP AMP 16-14 APPROX AS SHOWN

2 WIRE INSULATION DIA: 2.9-4.3 [.115-.170]

3 TONGUE MATERIAL THK: 0.78±0.05 [.031±.002]

4 BODY & SLEEVE: TIN PLATE PER ASTM B545,

5 BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON, COLOR - BLUE

6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

1000		LOOSE PIECE		160170	
QTY		PACKAGE TYPE		PART NO	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 02DEC09		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK T MICHIELUTTI 02DEC09	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		VOLTAGE RATING: -		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED		APVD T MICHIELUTTI 02DEC09	
FOR ORDER ENTRY		1-800-526-5142		MATERIAL - 5		FINISH - 4		NAME TERMINAL, RECTANGULAR TONGUE, PIDG, WIRE SIZE: 16-14 AWG	
		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	
								SIZE A3	
								CAGE CODE 00779	
								DRAWING NO C-160170	
								RESTRICTED TO -	
								SCALE 4:1	
								SHEET 1 OF 1	
								REV D	

CUSTOMER DRAWING