


5mm photodiode PD333-3C/H0/L2

Features

- Fast response time
- High photo sensitivity
- Small junction capacitance
- Pb free
- The product itself will remain within RoHS compliant version
- Compliance with EU REACH



Description

- PD333-3C/H0/L2 is a high speed and high sensitive PIN photodiode in a standard 5Φ plastic package. Due to its water clear epoxy the device is sensitive to infrared radiation

Applications

- High speed photo detector
- Security system
- Camera

Device Selection Guide

Chip Materials	Lens Color
Silicon	Water clear

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V_R	32	V
Operating Temperature	T_{opr}	-25 ~ +85	°C
Storage Temperature	T_{stg}	-40 ~ +100	°C
Soldering Temperature	T_{sol}	260	°C
Power Dissipation at (or below) 25°C Free Air Temperature	P_c	150	mW


Electro-Optical Characteristics (Ta=25°C)


Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Range Of Spectral Bandwidth	$\lambda_{0.5}$	400	-----	1100	nm	-----
Wavelength Of Peak Sensitivity	λ_p	-----	940	-----	nm	-----
Open-Circuit Voltage	V_{OC}	-----	0.39	-----	V	Ee=1mW/cm ² λ_p =940nm
Short- Circuit Current	I_{SC}	-----	40	-----	μA	Ee=1mW/cm ² λ_p =940nm
Reverse Light Current	I_L	36	40	-----	μA	Ee=1mW/cm ² λ_p =940nm V_R =5V
Reverse Dark Current	I_D	----	5	30	nA	Ee=0mW/cm ² V_R =10V
Reverse Breakdown Voltage	V_{BR}	32	170	-----	V	Ee=0mW/cm ² I_R =100μA
Total Capacitance	C_t	-----	18	-----	pF	Ee=0mW/cm ² V_R =5V f=1MHz
Rise Time/ Fall Time	t_r / t_f	-----	45/45	-----	ns	V_R =10V R_L =100Ω
View Angle	2θ1/2	-----	80	-----	deg	I_F =20mA

Note:


Tolerance of Luminous Intensity: ±10%
Tolerance of Dominant Wavelength: ±1nm
Tolerance of Forward Voltage: ±0.1V

Typical Electro-Optical Characteristics Curves






Package Dimension



Note: Tolerances unless dimensions ± 0.25 mm

Label Form Specification




- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number
- X: Month
- Reference: Identify Label Number

Packing Quantity Specification


■ Anti-electrostatic bag



■ Inner Carton



■ Outside Carton



1.200~500PCS/1Bag , 5Bags/1 Inner Carton
2.10 Inner Cartons/1 Outside Carton

DISCLAIMER

1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.