


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART
CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F005	Effective: 12/21/98				DCP No. 880
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
170	A	RELEASED	HYO	1/21/00	JJC	2/16/00	DJC	2/24/00	

Specifications:

- 1. Color: Red
- 2. Insulator: Polyacetal
- 3. Jack Body: Brass, nickel plated
- 4. Nut: Brass, nickel plated
- 5. Voltage: 500V
- 6. Current: 36A max.
- 7. Temperature: -20°C to +80°C



DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION
AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE
BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE
INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Tolerances Unless

Otherwise Specified

Fractions ± 1/32

Decimals

.XX ± .01

.XXX ± .005

DRAWING TITLE:

4mm Insulated Jack, Solder

SIZE DWG. NO.

A

2298

ELECTRONIC FILE

92N4660.dwg

REV

A