


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

④ PANDUIT PART NUMBER	PACKAGE QUANTITY	MINIMUM BUNDLE DIAMETER	MAXIMUM BUNDLE DIAMETER	LENGTH = "L" ±.2 [5]
MLT2.7WH-LP316	50	2.0" [51]	2.7" [69]	10.2" [259]
MLT4WH-LP316	50	2.0" [51]	4.0" [102]	14.3" [362]
MLT6WH-LP316	50	2.0" [51]	6.0" [152]	20.5" [521]
MLT8WH-LP316	50	2.0" [51]	8.0" [203]	26.8" [679]
MLT10WH-LP316	50	2.0" [51]	10.0" [203]	33.0" [838]




NOTES:

- 1.) APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
- 2.) MINIMUM LOOP TENSILE STRENGTH - 450 LBS (2000 NEWTONS)
ALL PARTS WHEN TESTED ON A 3" MANDREL EXCEPT
PART NO. MLT2.7WH-LP316 WHEN TESTED ON A 1 1/2" MANDREL.
- 3.) [] DENOTES DIMENSION IN MILLIMETERS
- 4.) TOLERANCES:
.XXX = ±.010 [.25]
.XX = ±.02 [.5]
.X = ±.03 [.8]
ANGLES = ±2°
- 5.) MATERIAL: 316 STAINLESS STEEL

SECTION "A-A"
4X SCALE

FULLY ROUNDED
EDGES ALONG
STRAP BODY

05A	3/13	JAMB	MIM	RGRO	ORIG CAD FILE SPEC WAS S41123-04. UPDATED DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037
04	3/07	JAMB	SKB	---	⑤ REMOVED PANDUIT PART NO. MLT2.7WH-TL316, MLT4WH-TL316 & MLT6WH-TL316 PACKAGE QTY 250	SS00338
03	11/06	JAMB	DPN	---	⑤ ADDED PANDUIT PART NO. MLT2.7WH-TL316, MLT4WH-TL316 & MLT6WH-TL316 PACKAGE QTY 250	SS00281
02	9/04	JAMB	DPN	JJB	⑥ REMOVED "AISI NO. 1 FULL RADIUSED" & REPLACED W/ "FULLY ROUNDED". ③ ADDED "REF" TO DIM ④ mm was [50]	12052
01	10/03	BRH	DPN	JJB	① ADDED ST3MT TO APPLICATION TOOL NOTE	11162
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		WAVE-TY HEAVY SERIES 316 STAINLESS STEEL				CUSTOMER DRAWING	
ITEM REVISION NAME		N41123BS/05		PANDUIT			
DATASET FILE NAME		N41123BS/05					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:			
.x ± .1 [2.54] .xx ± .01 [.25]				316 STAINLESS STEEL			
.xxx ± .005 [.127] ANGLES ± 5 °				DRAWING NUMBER:			
				N41123BS_DC			
THIRD ANGLE PROJECTION							
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE	
JAMB	10/03	DPN	2:1			A	