




REV 1 11/21/97

COIL:

RESISTANCE 1560 OHMS $\pm$ 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 17.0 VDC

MUST RELEASE _____

ENVIRONMENT:

VIBRATION 10 CPS TO 500 CPS @ 10 g's


SHOCK 30 g's 6 MS. DURATION

TEMPERATURE -55 °C TO +85 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 6.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000
OPERATIONS

DR. R.B. 11/24/97 CK 11/24/97

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD

CUST. NO. _____

TYPE "HMD" RELAY

HMD2-26B