

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GO	00		R1	REVISED PER ECO-11-005140	25MAR11	RK	HMR

1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.

2. ALL DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.





3. MATERIAL: HOUSING — THERMOPLASTIC.
TERMINAL — HIGH STRENGTH COPPER ALLOY PLATED WITH 0.76µm [.000030] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, 0.76µm [.000030] MIN TOTAL ON MATING SURFACE, OVER 1.27µm [.000050] MIN NICKEL PLATING.

4. WIRE SIZE: 24 & 26 AWG SOLID OR 24 AWG 7 STRANDS OF COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF 1.14[.045] IS ACCEPTABLE FOR MOST APPLICATIONS.


5. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.

TERMINAL
QUANTITY 50

BLUE COLOR DOT
LOCATED IN CENTER



GRAY	229975-4
BLACK	229975-1
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S. DOSS	12 FEB 80	 TE Connectivity							
		CHK	V.E. SLACK	14 FEB 80								
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:			NAME RECEPTACLE ASSEMBLY, 50 POSITION, B-SLOT, WITH 4-40 HOLES, CHAMP-LOK®							
		APVD B. WARD 14 FEB 80										
		PRODUCT SPEC —										
		APPLICATION SPEC —										
		—										
MATERIAL		FINISH			SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
					WEIGHT	—	A2	00779	C=229975	—		
CUSTOMER DRAWING						SCALE	2:1		SHEET	1 of 1	REV	R1