

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

74752-2701

Status:

Active

Overview:

SFP+ Passive Cable Assembly

Description:

SFP+ Passive Cable Assembly, 10Gbps, 28 AWG Cable, Pull-to-Release Plunger Style Latch, 7.0m Length



image - Reference only

Series

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E72548
General	
Product Family	Cable Assemblies
Series	74752
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	SFP Plus-to-SFP Plus
Overview	SFP+ Passive Cable Assembly
Product Name	SFP Plus
UPC	800756660905
Physical	
Cable Length	7.0m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Beryllium Copper, Zinc Alloy
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Twin-ax
Electrical	
Impedance	100#
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	3.3V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-74752-001

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

74752Series

Mates With

74441 SFP Plus (SFP+) Host Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74752-2701](#)