






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	BY	APP'D
		A		FIRST VERSION	23NOV2015	GF	SM



NOTES :

△ MATERIALS AND FINISH:

1. HOUSING: PA66
2. CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
3. MUST COMPLY WITH DIRECTIVE 2002/95/EC (RoHS)
4. WIRE TYPES AND SIZES ACCEPTED
5. WIRE RANGE: 14AWG~28AWG.
6. STRIP LENGTH: 10mm
7. PACKAGED IN TRAY.
8. CURRENT RATING: 16Amp AC300V.
9. OPERATION TEMPERATURE: -40°C TO +105°C
10. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834078
11. THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834078

PCB Layout

DIM A	NO. OF POSITIONS	PART NO
41.00	8 POSN	284078-7
36.00	7 POSN	284078-6
31.00	6 POSN	284078-5
26.00	5 POSN	284078-4
21.00	4 POSN	284078-3
16.00	3 POSN	284078-2
11.00	2 POSN	284078-1

④	SPRING
③	COVER
②	CONTACT
①	HOUSING

THIS DRAWING IS A CONTROLLED DOCUMENT			
DESIGNED BY	CHENGE FU	23NOV2015	TE Connectivity
APPROVED BY	SHI JIANG	23NOV2015	
PRODUCT CODE	108-137146		
APPLICATION SPEC	114-137146		
VERSION	-		
CUSTOMER DRAWING	A200779	C-2834078	
SCALE	1:1	SHEET	1 OF 1
REV	A		