


5

4

3

2

1



Wire _____ Cu tinned

Gauge _____ AWG 28/7

Voltage rating _____ 300 Vr.m.s

Current (Max) _____ 2,1A

Conductor resistance _____ 221 mΩ/m

Capacity unbalanced _____ 42,7 pF/m

Impedance unbalanced _____ 105 Ω

Inductance unbalanced _____ 0,68 μH/m

Signal delay _____ 4,9 ns/m

Insulation material _____ PVC

Temperature rating _____ -20°C (operating) to 105°C
 _____ -30°C (static)

Flammability rating _____ UL: VW1

Insulation resistance _____ 100 MΩ/km

Approval _____ UL AWM style 2651

Colour code sequence (in 10 steps):

- brown
- red
- orange
- yellow
- green
- blue
- violet
- grey
- white
- black

				Dat.	Name		SEK 18 Flat cable	Maßstab/ Scale	
			Detail.	20/10/05	JMDR		All Dim. in mm Orig. Size DIN A 4	26 poles, length per reel: 30,48 m colour coded, UL 20130, IEC 918	10:1
			Insp.						
EC01446	12/02/10	SC	Stand.						
33990	14/05/07	PK	HARTING EURL F-95972 Paris					TB 09 18 026 7005	Blatt/ Page
33246	20/10/05	JMDR							
Mod.	Dat.	Name					Sub.		

HARTING EURL
F-95972 Paris



TB 09 18 026 7005

Sub.

Blatt/ Page
1 / 1