

SOT-89



Pin Definition:

1. Ground
2. Input
3. Output

SOT-223



Pin Definition:

1. Input
2. Ground
3. Output

General Description

TS9013 is a positive voltage regulator developed utilizing CMOS technology featured very low power consumption, low dropout voltage and high output voltage accuracy. Built in low on-resistor provides low dropout voltage and large output current. A 2.2uF or greater can be used as an output capacitor.

TS9013 are prevented device failure under the worst operation condition with both thermal shutdown and current fold-back. These series are recommended for configuring portable devices and large current application, respectively.

Features

- Output current up to 500mA
- Low power consumption, 15uA(typ) @Vo=5V
- Output voltage $\pm 2\%$
- Internal current limit
- Thermal shutdown protection

Applications

- Palmtops
- Video recorders
- Battery powered equipment
- PC peripherals
- CD-ROM, DVD ROM
- Digital signal camera

Ordering Information

Part No.	Package	Packing
TS9013 $\underline{x}$ CW RP	SOT-223	2.5Kpcs / 13" Reel
TS9013 $\underline{x}$ CY RM	SOT-89	1Kpcs / 7" Reel

Note: Where $\underline{x}$ denotes voltage option, available are

D=1.8V


K=2.5V

S=3.3V


5=5.0V

Contact factory for additional voltage options.

Block Diagram



Typical Application Circuit



Absolute Maximum Rating

Parameter		Symbol	Limit	Unit
Input Supply Voltage		V_{IN}	12	V
Input Operating Voltage		V_{IN} (opr. Typ.)	10	
Output Current		I_O	500	mA
Power Dissipation (without heat sink)	SOT-89	P_D	0.5	W
	SOT-223		0.7	
Operating Junction Temperature Range		T_J	-40 ~ +150	°C
Storage Temperature Range		T_{STG}	-65 ~ +150	°C
Lead Soldering Temperature (260°C)			5	S

Notes: Stress above the listed absolute rating may cause permanent damage to the device.


Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Conditions		Min	Typ	Max	Unit
Output Voltage	V _{IN} =Vo + 1V, Io =1mA,	TS90135	4.90	5.0	5.10	V
		TS9013S	3.23	3.3	3.36	
		TS9013K	2.45	2.5	2.55	
		TS9013D	1.76	1.8	1.83	
Maximum Output Current	V _{IN} =Vo+1V,		500	--	--	mA
Input Stability	V _O +1V ≤ Vin ≤ V _O +2V, Io=1mA		--	0.2	0.3	%
Load Regulation (Note1)	V _{IN} =Vo+1V, 1mA≤IL≤500mA	TS90135	--	40	80	mV
		TS9013S				
	V _{IN} =Vo+1V, 1mA≤IL≤500mA	TS9013K	--	40	90	
		TS9013D				
Dropout Voltage (Note 2)	Io=300mA	TS90135	--	300	500	mV
		TS9013S				
	Io=500mA	TS90135	--	500	600	
		TS9013S				
	Io=500mA	TS9013K	--	600	850	
		TS9013D	--	600	850	
Quiescent Current	V _{IN} =Vo+1V, Io=0A		--	15	25	uA
Output Current Limit	V _{OUT} < 0.4V		550	--	--	mA
Power Supply Rejection Ratio	At f=100KHz, Io=10mA,		--	30	--	dB
Output Voltage Temperature Coefficient (Note 3)			--	100	--	ppm/°C

Notes:


- Regulation is measured at constant junction temperature, using pulsed ON time.
- Dropout is measured at constant junction temperature, using pulsed ON time, and the criterion is V_{OUT} inside target value $\pm 2\%$.

SOT-89 Mechanical Drawing





SOT-89 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.40	4.60	0.173	0.181
B	1.40	1.75	0.055	0.069
C	2.40	2.60	0.094	0.102
D	0.36	0.48	0.014	0.018
E	1.40	1.60	0.054	0.063
F	2.90	3.10	0.114	0.122
G	0.89	1.20	0.035	0.047
H	--	4.25	--	0.167
I	1.40	1.60	0.055	0.068
J	0.38	0.43	0.014	0.017

Marking Diagram




- Y** = Year Code
- M** = Month Code
(A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
- L** = Lot Code
- X** = Fixed Output Voltage Code
D=1.8V, K=2.5V, S=3.3V, 5=5.0V.

SOT-223 Mechanical Drawing



SOT-223 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	6.350	6.850	0.250	0.270
B	2.900	3.100	0.114	0.122
C	3.450	3.750	0.136	0.148
D	0.595	0.635	0.023	0.025
E	4.550	4.650	0.179	0.183
F	2.250	2.350	0.088	0.093
G	0.835	1.035	0.032	0.041
H	6.700	7.300	0.263	0.287
I	0.250	0.355	0.010	0.014
J	10°	16°	10°	16°
K	1.550	1.800	0.061	0.071

Marking Diagram



- Y** = Year Code
- M** = Month Code
(A=Jan, B=Feb, C=Mar, D=Apr, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
- L** = Lot Code
- X** = Fixed Output Voltage Code
18=1.8V, 25=2.5V, 33=3.3V, 50=5.0V.

TS9013

500mA Low Quiescent Current CMOS LDO

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[TS90135CW](#) [TS90135CY](#) [TS9013DCY](#) [TS9013KCW](#) [TS9013KCY](#) [TS9013SCW](#) [TS9013SCY](#)