

# Disc Ceramic Capacitors



## Professional Ceramic Capacitors - Class I, II and III

### MIL-STD-202F

The professional ceramic disc capacitors were specially developed for applications in severe environmental conditions, high humidity, temperature, gas, vapor and solvents.

The capacitors are flame retardant epoxy coated, meeting UL 94-V0 flammability specifications. The capacitors are 100% screened on following electrical parameters:

Capacitance, loss factor, test voltage. After the 100% test, the capacitors are audited on its electrical and mechanical parameters with following AQL:

Electrical parameters: 0.065% level II

Mechanical parameters: 0.65% level II

The capacitors withstand the following reliability essays:

Terminal strength: method 211 – condition A

Resistance to solvents: method 215

Resistance to soldering heat: method 210 – condition B


Solderability: method 208

Thermal shock: method 107 – condition A

Humidity (steady state): method 103 – condition D

Life (at elevated ambient temperature): method 108 – condition D

Operating temperature and storage: -55... +125° C



millimeters (inches)		
Lead Spacing	Digit 8	
F		
2.5 (0.100)	D	—
5 (0.200)	A	O
6 (0.250)	E	X
7.5 (0.300)	B	R
10 (0.400)	C	W

DIMENSIONS			
Digit 9 (Ø)	D ± 2 (0.079)	T max.	Available Lead Spacing
A <sup>NPO</sup> 1pF... 2.7 pF	4.0 (0.157)	3.0 (0.118)	A,B,D,E,O,R
A <sup>N1500</sup> 5.6pF... 8.2 pF	4.0 (0.157)	3.0 (0.118)	A,B,D,E,O,R
A Others	4.0 (0.157)	3.0 (0.118)	A,B,D,E,O,R
B	5.0 (0.197)	3.0 (0.118)	A,B,D,E,O,R,X
C	6.0 (0.236)	3.0 (0.118)	A,B,C,D,E,O,R,X
D	7.0 (0.276)	3.0 (0.118)	A,B,C,D,E,O,R,X
E	8.0 (0.315)	3.0 (0.118)	A,B,C,D,E,O,R,X
F	9.0 (0.354)	3.0 (0.118)	A,B,C,E,O,R,X
G	10.0 (0.394)	3.0 (0.118)	A,B,C,E,O,R,X
H	11.0 (0.433)	3.0 (0.118)	A,B,C,E,O,R,W
J	13.0 (0.512)	3.5 (0.138)	B,C,R,W
K	15.0 (0.591)	3.5 (0.138)	B,C,R,W
M	19.0 (0.748)	4.0 (0.157)	B,C

(E), (X), (W): upon request

# Disc Ceramic Capacitors



## General Specifications - Class III Professional

### DIELECTRIC - CLASS III


A thin dielectric layer is grown on a disc of conductive ceramic. Very large capacitances can be obtained due to reduced thickness of this barrier layer and its inherently high dielectric constant. Due to its small dimensions, they are a less expensive replacement of multilayer ceramic or polyester capacitors.

### DIMENSIONS

millimeters (inches)

Digit 9 of P.N. (ø)	D ± 2 (0.079)	T max.	Available Lead Spacing
A	4.0 (0.157)	3.0 (0.118)	A,B,D,E,O,R
B	5.0 (0.197)	3.0 (0.118)	A,B,D,E,O,R,X
C	6.0 (0.236)	3.0 (0.118)	A,B,C,D,E,O,R,X
D	7.0 (0.276)	3.0 (0.118)	A,B,C,D,E,O,R,X
E	8.0 (0.315)	3.0 (0.118)	A,B,C,D,E,O,R,X
F	9.0 (0.354)	3.0 (0.118)	A,B,C,E,O,R,X
G	10.0 (0.394)	3.0 (0.118)	A,B,C,E,O,R,X
H	11.0 (0.433)	3.0 (0.118)	A,B,C,E,O,R,W
J	13.0 (0.512)	3.5 (0.138)	B,C,R,W
K	15.0 (0.591)	4.0 (0.157)	B,C,R,W

(E), (X), (W): upon request



millimeters (inches)		
Lead Spacing	Digit 8 of P.N.	
F		
2.5 (0.100)	D	—
5 (0.200)	A	O
6 (0.250)	E	X
7.5 (0.300)	B	R
10 (0.400)	C	W

### PERFORMANCE CHARACTERISTICS CLASS III

Measured at	1.0 kHz / 0.1 Vrms / 25°C	
Dissipation Factor	$C_R \leq 22 \text{ nF} \rightarrow Y5V, Y5U \leq 7.5\%$ $C_R > 22 \text{ nF} \rightarrow Y5V, Y5P \leq 5.0\%$	
Capacitance Tolerance	$Y5P \rightarrow \pm 20\% / -20 +50\%$ $Y5U \rightarrow \pm 20\% / -20 +80\%$ $Y5V \rightarrow \pm 20\% / -20 +80\%$	
Climatic Category	55 / 085 / 56	
Insulation Resistance @ $V_R$	Y5P	$\geq 12 \text{ M}\Omega$
	Y5U	$4.7 \text{ nF} \dots 100 \text{ nF} \rightarrow \geq 10 \text{ M}\Omega$ $200 \text{ nF} \rightarrow \geq 1 \text{ M}\Omega$
	Y5V	$\geq 100 \text{ M}\Omega$
Dielectric Strength NOTE: Charging current limited to 50 mA	Between leads	$V_t = 1.25 V_R$
	Body insulation	$V_R = 25V \quad V_t = 100V \text{ (DC)}$ $V_R = 50V \quad V_t = 150V \text{ (DC)}$
Operating Temperature Range (°C)	-55... +125 Epoxy Coated	

Note: Damp Heat Steady State: 90... 95% R.H. 40°C / 21 days. No voltage to be applied.

# Disc Ceramic Capacitors

## Dimension Table

### Barrier Layer Capacitors - Class III Professional



#### EPOXY COATED – CAPACITANCE VS. DISC DIAMETER

millimeters (inches)

Class III	Δ C/C (max.) ±12%	Range -30... +85°C	Δ C/C (max.) +30 -65%	Range -30... +85°C	Δ C/C (max.) +22 -85%	Range -30... +85°C
Temp. Coefficient	Y5P		Y5U		Y5V	
Digits 1,2,3 of P.N.	6WF	6WH	6YF	6YH	6ZH	
Rated Voltage (V <sub>R</sub> )	25	50	25	50	50	
C <sub>R</sub> (pF)						
4,700	4.0 (0.157)	4.0 (0.157)	4.0 (0.157)	4.0 (0.157)	4.0 (0.157)	4.0 (0.157)
10,000	6.0 (0.236)	6.0 (0.236)				
22,000	7.0 (0.276)	8.0 (0.315)		5.0 (0.197)	6.0 (0.236)	
33,000	8.0 (0.315)	9.0 (0.354)		6.0 (0.236)	7.0 (0.276)	
47,000	10.0 (0.394)	11.0 (0.433)		7.0 (0.276)	8.0 (0.315)	5.0 (0.197)
50,000		—				
68,000	11.0 (0.433)	13.0 (0.512)	13.0 (0.512)	—	7.0 (0.276)	7.0 (0.276)
100,000	13.0 (0.512)	15.0 (0.591)				
200,000	—	—				

Y5U, Y5V - Preferences


Diameter (φ) = 9th Part Number Digit

# Disc Ceramic Capacitors



## Ordering Code

### HOW TO ORDER



\*Upon Request

# Disc Ceramic Capacitors



## Ordering Code

**M**



**Tolerance**  
 C =  $\pm 0.25$  pF  
 D =  $\pm 0.50$  pF  
 J =  $\pm 5\%$   
 K =  $\pm 10\%$   
 M =  $\pm 20\%$   
 S = -20+50%  
 Z = -20+80%  
 P = 0+100%

**A**



Lead Forming				
mm	inches	D	O	N
2.5 $\pm 0.5$	.1 $\pm .025$	D	—	—
5 $\pm 0.6$	.2 $\pm .025$	A	O	N
6 $\pm 0.6$	.25 $\pm .025$	E	X	—
7.5 $\pm 1$	.3 $\pm .05$	B	R	Q
10 $\pm 0.5$	.4 $\pm .05$	C	W	—
12.5 $\pm 1$	.5 $\pm .05$	P	—	—

**E**



**Capacitor Diameter**  
 $\pm 2$  (0.079)  
 A = 4 (0.157)  
 B = 5 (0.197)  
 C = 6 (0.236)  
 D = 7 (0.276)  
 E = 8 (0.315)  
 F = 9 (0.354)  
 G = 10 (0.394)  
 H = 11 (0.433)  
 J = 13 (0.512)  
 K = 15 (0.591)  
 M\* = 19 (0.748)


\*Wire 0.8 (0.031) recommended

**A**



**Packaging**

### Cardboard Strips



### Bulk

**E** = 5 (0.197)  $\pm 1$  (0.039) free wire length  
**C** = 10 (0.394)  $\pm 1$  (0.039) free wire length  
**D** = 25 (0.984)  $\pm 1$  (0.039) free wire length

### Taping



### Reel

Avisert		Panasert	
H	L	L	J




### Ammo Pack

Avisert		Panasert	
I	M	M	K


### Finishing

Diam  $\leq 9$  (0.354) and  
 F = 5.00 (0.197)

For every other:



Coating does not  
 surpass the bend



### Low Voltage

A = Phenolic (General Purpose) Q = Waxed phenolic

S = Epoxy (Professional) cap. diameter  
 $\leq 8$  (0.315)

D = Epoxy (Professional) cap. diameter  
 $> 8$  (0.315)

### High Voltage



F = Measured  
 from the  
 center of  
 leads

C = Epoxy wire diameter 0.6 0.1  
 $(0.024) \pm (0.004)$

I = Epoxy wire diameter 0.8 0.1  
 $(0.031) \pm (0.004)$

L = Phenolic wire diameter 0.6 0.1  
 $(0.024) \pm (0.004)$

Please note that not all code combinations  
 are either possible or available.

# Disc Ceramic Capacitors




## Marking

DIG. 2	
O	
TC / Class	
General Purpose	Professional
A = NP0 / I	A = NP0 / I
*B = P100 / I	B = P100 / I
*C = N150 / I	C = N150 / I
*D = N220 / I	D = N220 / I
*E = N330 / I	E = N330 / I
*F = N470 / I	F = N470 / I
G = N750 / I	G = N750 / I
H = N1500 / I	H = N1500 / I
*I = N2200 / I	I = N2200 / I
*J = N4700 / I	J = N4700 / I
K = SL	7 = Y5U / SM
M = Y5E / II	8 = Y5V / SM
N = Y5F / II	L = Y5P / SM
O = Y5P / II	M = X5E / II
P = Y5R / II	N = X5F / II
Q = Y5T / II	O = X5P / II
S = Y5U / II	P = X5R / II
T = Y5V / II	Q = X5T / II
U = Z5V / II	S = X5U / II
V = Z4V / III	T = X5V / II
*W = Y5P / II	U = Z5V / II
*X = Y5R / II	V = Z4V / III
Y = Y5U / II	W = Y5P / III
Z = Y5V / II	X = Y5R / III
	Y = Y5U / III
	Z = Y5V / III

\*Upon Request

Logo: Only in diam.  $\geq$  6mm



Rated Voltage
D = 16V
F = 25V
H = 50V
K = 100V
Q = 500V
R = 1000V
S = 2000V
T = 3000V
U = 4000V
W = 5000V
X = 6000V
Y = 7500V

Tolerance
C = $\pm 0.25\text{pF}$
D = $\pm 0.5\text{pF}$
J = $\pm 5\%$
K = $\pm 10\%$
M = $\pm 20\%$
S = $-20 +50\%$
Z = $-20 +80\%$
P = $0 +100\%$

Capacitance	EIA
1pF = 109	100pF = 101
1.2pF = 129	120pF = 121
1.5pF = 159	150pF = 151
1.8pF = 189	180pF = 181
2.2pF = 229	220pF = 221
2.7pF = 279	270pF = 271
3.9pF = 399	390pF = 391
4.7pF = 479	470pF = 471
5.6pF = 569	560pF = 561
6.8pF = 689	680pF = 681
8.2pF = 829	820pF = 821
10pF = 100	1nF = 102
12pF = 120	1.2nF = 122
15pF = 150	1.8nF = 182
18pF = 180	2.2nF = 222
22pF = 220	2.7nF = 272
27pF = 270	3.9nF = 392
39pF = 390	4.7nF = 472
47pF = 470	5.6nF = 562
56pF = 560	6.8nF = 682
68pF = 680	8.2nF = 822
82pF = 820	10nF = 103
	15nF = 153
	22nF = 223
	33nF = 333
	47nF = 473
	100nF = 104
	200nF = 204

TC – Temperature coefficient.

DIG – for better understanding, check pages 3 and 4.

### Safety Front

Capacitance
As above

As above

Type
61V
620
65N

Tolerance
As above

Back: (Approval marks)


# Disc Ceramic Capacitors



## Packaging

### IDENTIFICATION AND TRACEABILITY

On all TPC ceramic capacitors packages, you will find a bar code label with the following information:



### TAPED PARTS QUANTITY TABLE

millimeters (inches)

Rated Voltage (Vr)	Diameter D	Quantities	
		Ammopack	Reel
Vr <= 500V	D ≤ 7 (0.276)	2000	2500
	7 < D ≤ 11 (0.433)	2000	2000
500V < Vr <= 2KV	D ≤ 11 (0.433)	1500	2000
	D ≤ 11 (0.433)	1000	1500

### CARDBOARD STRIPS QUANTITY TABLE

millimeters (inches)

Rated Voltage (Vr)	Diameter D	Lead Space	
		< = 5 (0.197)	> 5 (0.197)
Vr <= 500V	D ≤ 8 (0.315)	2500	1500
	8 (0.315) ≤ D ≤ 11 (0.433)	1500	-
	8 (0.315) ≤ D ≤ 13 (0.512)	-	1000
	11 (0.433) ≤ D ≤ 15 (0.591)	1000	-
	13 (0.512) ≤ D ≤ 19 (0.748)	-	500
	D ≤ 19 (0.748)	500	-
500V < Vr <= 2KV	D ≤ 9 (0.354)	1500	1000
	9 (0.354) ≤ D ≤ 11 (0.433)	-	1000
	9 (0.354) ≤ D ≤ 13 (0.512)	1000	-
	11 (0.433) ≤ D ≤ 19 (0.748)	-	500
	13 (0.512) ≤ D ≤ 19 (0.748)	500	-
2KV < Vr <= 5KV Safety 65N 620	D ≤ 9 (0.354)	1500	-
	D ≤ 11 (0.433)	-	1000
	D ≤ 13 (0.512)	500	500
Safety 61V	D ≤ 6 (0.236)	1500	1500
	7 (0.275) ≤ D ≤ 9 (0.354)	1000	1000
	9 (0.354) ≤ D	500	500

Quantities for other package alternative, upon request.


# Disc Ceramic Capacitors



## Tape and Reel Specifications

There are two types of taped disc ceramic capacitors:  
Straight or crimped leads.

Both types can be shipped on reels or ammopack.  
The standard packaging quantities are shown below:



Digit 11	Available Tapings	Digit 9
L	Sizes      4 (0.157) $\leq$ D $\leq$ 11 (0.433)	A... H
M		
J H	Sizes      6 (0.236) $\leq$ D $\leq$ 11 (0.433)	C... H
K I		

## TPC Code    Digit 11

Packaging	Avisert	Panasert
Reel	 FIGURE 1   FIGURE 2   FIGURE 3	 FIGURE 1   FIGURE 2   FIGURE 3
Ammopack	 FIGURE 1   FIGURE 2   FIGURE 3	 FIGURE 1   FIGURE 2   FIGURE 3

Figure 2: Inside Crimp 100V... 1000V

Figure 3: Outside Crimp 1000V

# Disc Ceramic Capacitors




## Tape and Reel Specifications


millimeters (inches)

Description of Symbols	Straight Leads		Crimped
	Figure 1		Figure 2 & 3
	A (Avisert)	P (Panasert)	Avisert & Panasert
Crimp angle	$\infty$	—	20°...45°
Crimp length	C	—	1.7 min.
Lead diameter	d	0.60 ± 0.1	
Disc diameter	D	11 max.	
Lead hole diameter	Do	4.0 ± 0.2	
Disc thickness	T	See Catalog	
Lead spacing	F	5.0 <sup>+0.6</sup> <sub>-0.2</sub>	
Component alignment, front-rear	$\Delta h$	0 ± 1	
Height of component from tape center	H	19.5 ± 0.5	16.5 ± 0.5 - 0
Height from tape center to crimp	Ho	—	16 + 0.5 - 0
Component height	H1	32.25 max.	>23.5 <32.25
Distance from component leads to tape bottom	$\ell_1$	12 max.	
Tape width	W	18 <sup>+1</sup> <sub>-0.5</sub>	
Bonding tape width	W <sub>3</sub>	5.5 min.	
Feed hole position	W <sub>1</sub>	9.0 ± 0.5	
Pitch between discs	P	12.7 ± 1	
Feed hole pitch	Po	12.7 ± 0.3	
Hole center to lead	P1	3.85 ± 0.7	
Feed hole center to component center	P2	6.35 ± 1	
Tape + bonding tape thickness	t	0.7 ± 0.2	
Total tape thickness, including lead	t <sub>2</sub>	1.5 max.	

## PACKAGING



## SHIPPING CONTAINER



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AVX:](#)

[6WK103MODCL](#)