




AA17251 SERIES



External Dimensions



Frame:Aluminum Alloy
 Impeller:Plastic(UL:94V-0)
 Motor Structure:Shaded Pole Induction Motor.
 Motor Protection:Thermal Protect.
 Lead wire:UL1015AWG18
 Wire Type:-AT Terminal/ -AW Wires
 OPERATING TEMP*:-10°C~70°C
 *:-10°C~60°C for fans with sleeve/ball combination bearings.

Specifications(Nominal)


Frame size (mm)	Model No.	Bearing System Type	Volt. (VAC)	Freq. (Hz)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow		Maximum Pressure		*Noise Level (dB/A)	Weight (g)
								(CMM)	(CFM)	(InAq)	(mmAq)		
172x150X51	AA1751HB-AT	◎	115	50/60	0.52/0.47	40.90/36.70	2500/2800	5.546/5.943	196.0/210.0	0.425/0.266	10.795/6.756	52.3/53.0	930
	AA1752HB-AT		230		0.26/0.22	41.90/37.60							

Bearing type: ◎=Ball ⚙=Sleeve ●=Hypro bearing


Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
 (網頁上呈現產品軸承資訊均以2Ball為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)

50Hz



60Hz



*Safety approvals

				
✓	✓		✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AA1752HB-AT-LF](#) [AA1752HB-AW-LF](#)