


Technical data

- 1.Nominal voltage: 300V/30A
PITCH:9.5mm
- 2.Connection capacity:
AWG 22-10
- 3.Insulation Withstanding Voltage:
AC 2000V/MIN
- 4.Insulation Resistance:
1000MΩ or more at DC500V
- 5.Tightening torque:
10.0kgf.cm (1.0N.m)
- 6.Screw thread: M3.5
- 7.Operating temperature range:-40°C ~ 115°C
Soldering temperature:250°C±10°C /5s
- 8.Undimensioned Tolerances:

Dim.L=(P-1)x9.5+11.5 Dim.B=(P-1)x9.5 P= number of poles		
0-30mm	±0.20	±0.25
over 30mm-60mm	±0.25	±0.30
over 60mm-90mm	±0.30	±0.40
over 90mm-180mm	±0.40	±0.50
over 180mm	±0.50	±0.60

- 9.Safety approval: 
- 10.RoHS Compliance

Part No.: OSTYK511XX030

No. of Poles
02 2 Poles
03 3 Poles
... ..
24 24 Poles

3	SCREW+WASHER	STEEL	M3.5x0.6, Ni Plated	P
2	CONTACT	BRASS	M3.5x0.6, Tin PLATED	P
1	BODY	PA66 UL94V-0	Black	1
ITEM	NAME OF PART	MATERIAL	NOTES	Q"TY
DWG	WF. Zhang	DATE 2016.04.20	UNITS: MM	SHEET: 1 OF 1
CHK.	WF. Zhang	DATE 2016.04.20	SCALE: NONE 2:1 (:)	REV: A
APP.		DATE	TITLE: OSTYK511 Series middle contact pin type	X. ±0.50
			PART NO. OSTYK511XX030	X.X ±0.30
			DWG NO. OSTYK511XX030.dwg	X° ±1°

△			
SIGN	DESCRIPTION	CHK.	DATE