





A

B

C

D




SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	G±0.25
09	30.81	24.99	16.96	16.79	10.96	5.90
15	39.14	33.32	25.18	25.12	19.18	5.90
25	53.03	47.04	39.12	38.84	33.12	5.70

Core range

SHELL	TIN LEAD P/N	LEAD FREE P/N	DESIGNATIONS
09	D09P24A4GV00	D09P24A4GV00LF	HEADER 9 CTS STRAIGHT -SOLDER TO BOARD-PCB HARPOON-SCREWLOCK UNC 4.40-ELEC.CONTIN.-PERFORM. LEVEL PL3
15	D15P24A4GV00	D15P24A4GV00LF	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK UNC 4.40-ELEC.CONTIN.-PERFORM. LEVEL PL3
25	D25P24A4GV00	D25P24A4GV00LF	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK UNC 4.40-ELEC.CONTIN.-PERFORM. LEVEL PL3

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JARRY	1995/08/11	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1995/08/11			0.XX	±0.1				
Chr	LEGARE	1995/08/11			0.XXX	±0.1				
Appr	LEGARE	1995/08/11	Product Family		D-SUB		ECN		LS06-0097	
							Spec ref -			
			title HDR DELTA D STD EUROPE			drawing no C01-8646-100-1			Rev. F	
			straight, solder type for PCB 1.6mm							
			catalog no -			CUSTOMER			sheet 1 of 1	

rev	ecn no	dr	date
D	-	SBA	2003/04/16
E	LS05-0056	LGO	2005/07/07
F	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-