

**SPEC**

Spec No.	TQ3C-8EAF0-E1DEU50-00
Date	April 14, 2010

**TYPE : TCG057VGLGA-G00**

< 5.7 inch VGA transmissive color TFT  
with LED backlight>

**CONTENTS**

1. Application
2. Construction and outline
3. Mechanical specifications
4. Absolute maximum ratings
5. Electrical characteristics
6. Optical characteristics
7. Interface signals
8. Input timing characteristics
9. Backlight characteristics
10. Lot number identification
11. Warranty
12. Precautions for use
13. Reliability test data
14. Outline drawing

Issued  
Date: Apr 22, 2010  
  
KYOCERA  
Hayato LCD Division

KYOCERA CORPORATION  
KAGOSHIMA HAYATO PLANT  
LCD DIVISION

This specification is subject to change without notice.  
Consult Kyocera before ordering.

Original Issue Date	Designed by: Engineering dept.			Confirmed by: QA dept.	
	Prepared	Checked	Approved	Checked	Approved
April 14, 2010	S. Maezura	<i>Y. Okkeda</i>	<i>D. Johnson</i>	J. Sakaguchi	<i>J. Saito</i>

Spec No.	Part No.	Page
TQ3C-8EAFO-E1DEU50-00	TCG057VGLGA-G00	-

## **Warning**

1. This Kyocera LCD module has been specifically designed for use only in electronic devices and industrial machines in the area of audio control, office automation, industrial control, home appliances, etc. The module should not be used in applications where the highest level of safety and reliability are required and module failure or malfunction of such module results in physical harm or loss of life, as well as enormous damage or loss. Such fields of applications include, without limitation, medical, aerospace, communications infrastructure, atomic energy control. Kyocera expressly disclaims any and all liability resulting in any way to the use of the module in such applications.
2. Customer agrees to indemnify, defend and hold Kyocera harmless from and against any and all actions, claims, damages, liabilities, awards, costs, and expenses, including legal expenses, resulting from or arising out of Customer's use, or sale for use, or Kyocera modules in applications.

## **Caution**

1. Kyocera shall have the right, which Customer hereby acknowledges, to immediately scrap or destroy tooling for Kyocera modules for which no Purchase Orders have been received from the Customer in a two-year period.

Spec No.	Part No.	Page
TQ3C-8EAF0-E1DEU50-00	TCG057VGLGA-G00	-

### Revision record

Date	Designed by : Engineering dept.			Confirmed by : QA dept.	
	Prepared	Checked	Approved	Checked	Approved
Rev.No.	Date	Page	Descriptions		

Spec No. TQ3C-8EAF0-E1DEU50-00	Part No. TCG057VGLGA-G00	Page 1
-----------------------------------	-----------------------------	-----------

## 1. Application

This document defines the specification of TCG057VGLGA-G00. (RoHS Compliant)

## 2. Construction and outline

LCD	: Transmissive color dot matrix type TFT
Backlight system	: LED
Polarizer	: Glare treatment
Additional circuit	: Timing controller, Power supply (3.3V input) (without constant current circuit for LED Backlight)

## 3. Mechanical specifications

Item	Specification	Unit
Outline dimensions 1)	134.5(W)×103.4(H)×8(D)	mm
Active area	115.2(W)×86.4(H) (14.4cm/5.7 inch(Diagonal))	mm
Dot format	640×(B,G,R)(W)×480(H)	dot
Dot pitch	0.06(W)×0.18(H)	mm
Base color 2)	Normally White	-
Mass	(TBD)	g

- 1) Projection not included. Please refer to outline for details.
- 2) Due to the characteristics of the LCD material, the color varies with environmental temperature.

## 4. Absolute maximum ratings

### 4-1. Electrical absolute maximum ratings

Item	Symbol	Min.	Max.	Unit
Supply voltage	V <sub>DD</sub>	0	4.0	V
Input signal voltage 1)	V <sub>IN</sub>	-0.3	6.0	V
LED forward current 2)	IF	-	100	mA

- 1) Input signal : CK, R0 ~ R5, G0 ~ G5, B0 ~ B5, HSYNC, VSYNC, ENAB, R/L, U/D
- 2) For each “AN-CA”
- 3) Do not apply reversed voltage.

### 4-2. Environmental absolute maximum ratings

Item	Symbol	Min.	Max.	Unit
Operating temperature 1)	T <sub>OP</sub>	-20	70	°C
Storage temperature 2)	T <sub>STO</sub>	-30	80	°C
Operating humidity 3)	H <sub>OP</sub>	10	4)	%RH
Storage humidity 3)	H <sub>STO</sub>	10	4)	%RH
Vibration	-	5)	5)	-
Shock	-	6)	6)	-

- 1) Operating temperature means a temperature which operation shall be guaranteed. Since display performance is evaluated at 25°C, another temperature range should be confirmed.
- 2) Temp. = -30°C < 48h , Temp. = 80°C < 168h  
Store LCD at normal temperature/humidity. Keep them free from vibration and shock. An LCD that is kept at a low or a high temperature for a long time can be defective due to other conditions, even if the low or high temperature satisfies the standard.  
(Please refer to “Precautions for Use” for details.)
- 3) Non-condensing
- 4) Temp. 40°C, 85%RH Max.  
Temp. > 40°C, Absolute humidity shall be less than 85%RH at 40°C.

5)

Frequency	10 ~ 55 Hz	Acceleration value (0.3 ~ 9 m/s <sup>2</sup> )
Vibration width	0.15mm	
Interval	10-55-10 Hz	1 minutes

2 hours in each direction X, Y, Z (6 hours total)

EIAJ ED-2531


- 6) Acceleration: 490 m/s<sup>2</sup>, Pulse width: 11 ms  
3 times in each direction: ±X, ±Y, ±Z  
EIAJ ED-2531

Spec No. TQ3C-8EAFO-E1DEU50-00	Part No. TCG057VGLGA-G00	Page 3
-----------------------------------	-----------------------------	-----------

## 5. Electrical characteristics


Temp. = -20 ~ 70°C						
Item	Symbol	Condition	Min.	Typ.	Max.	Unit
Supply voltage 1)	V <sub>DD</sub>	-	3.0	3.3	3.6	V
Current consumption	I <sub>DD</sub>	2)	-	(150)	(TBD)	mA
Permissive input ripple voltage	V <sub>RP</sub>	-	-	-	100	mV <sub>p-p</sub>
Input signal voltage 3)	V <sub>IL</sub>	"Low" level	0	-	0.3V <sub>DD</sub>	V
	V <sub>IH</sub>	"High" level	0.7V <sub>DD</sub>	-	V <sub>DD</sub>	V

1) V<sub>DD</sub>-turn-on conditions



2) Display pattern:

V<sub>DD</sub> = 3.3V, Temp. = 25°C



3) Input signal : CK, R0 ~ R5, G0 ~ G5, B0 ~ B5, H<sub>SYNC</sub>, V<sub>SYNC</sub>, ENAB, R/L, U/D

## 6. Optical characteristics


Measuring spot = 6.0mm, Temp. = 25°C

Item	Symbol	Condition	Min.	Typ.	Max.	Unit	
Response time	Rise	$\tau_r$	= 0°	-	10	-	ms
	Down	$\tau_d$	= 0°	-	25	-	ms
Viewing angle range View direction : 12 o'clock (Gray inversion)	UPPER	CR 5	-	80	-	deg.	
	LOWER		-	80	-		
	LEFT		-	80	-		
	RIGHT		-	80	-		
Contrast ratio	CR	= 0°	300	500	-	-	
Brightness	L	IF=60mA/Line	(TBD)	(400)	-	cd/m²	
Chromaticity coordinates	Red	x	= 0°	(0.56)	(0.61)	(0.66)	-
				(0.31)	(0.36)	(0.41)	
	Green	x	= 0°	(0.30)	(0.35)	(0.40)	
				(0.52)	(0.57)	(0.62)	
	Blue	x	= 0°	(0.09)	(0.14)	(0.19)	
				(0.06)	(0.11)	(0.16)	
	White	x	= 0°	(0.28)	(0.33)	(0.38)	
				(0.30)	(0.35)	(0.40)	


### 6-1. Definition of contrast ratio

$$CR(\text{Contrast ratio}) = \frac{\text{Brightness with all pixels "White"}}{\text{Brightness with all pixels "Black"}}$$


### 6-2. Definition of response time



### 6-3. Definition of viewing angle



### 6-4. Brightness measuring points



- 1) Rating is defined on the average in the viewing area. (measured point 1 ~ 5)
- 2) Measured 30 minutes after the LED is powered on. (Ambient temp. = 25°C)

Spec No. TQ3C-8EAFO-E1DEU50-00	Part No. TCG057VGLGA-G00	Page 6
-----------------------------------	-----------------------------	-----------

## 7. Interface signals

### 7-1. LCD

No.	Symbol	Description	I/O	Note
1	GND	GND	-	
2	CK	Clock signal for sampling each data signal	I	
3	H <sub>SYNC</sub>	Horizontal synchronous signal (negative)	I	
4	V <sub>SYNC</sub>	Vertical synchronous signal (negative)	I	
5	GND	GND	-	
6	R0	RED data signal (LSB)	I	
7	R1	RED data signal	I	
8	R2	RED data signal	I	
9	R3	RED data signal	I	
10	R4	RED data signal	I	
11	R5	RED data signal (MSB)	I	
12	GND	GND	-	
13	G0	GREEN data signal (LSB)	I	
14	G1	GREEN data signal	I	
15	G2	GREEN data signal	I	
16	G3	GREEN data signal	I	
17	G4	GREEN data signal	I	
18	G5	GREEN data signal (MSB)	I	
19	GND	GND	-	
20	B0	BLUE data signal (LSB)	I	
21	B1	BLUE data signal	I	
22	B2	BLUE data signal	I	
23	B3	BLUE data signal	I	
24	B4	BLUE data signal	I	
25	B5	BLUE data signal (MSB)	I	
26	GND	GND	-	
27	ENAB	Signal to settle the horizontal display position (positive)	I	1)
28	V <sub>DD</sub>	3.3V power supply	-	
29	V <sub>DD</sub>	3.3V power supply	-	
30	R/L	Horizontal display mode select signal L : Normal , H : Left / Right reverse mode	I	2)
31	U/D	Vertical display mode select signal H : Normal , L : Up / Down reverse mode	I	2)
32	NC	No connect	I	
33	GND	GND	-	

LCD connector

: IMSA-9681S-33A-GF (IRISO)

Recommended matching FFC or FPC

: 0.5mm pitch

Spec No.	Part No.	Page
TQ3C-8EAF0-E1DEU50-00	TCG057VGLGA-G00	7

1) The horizontal display start timing is settled in accordance with a rising timing of ENAB signal.  
In case ENAB is fixed "Low", the horizontal start timing is determined.  
Don't keep ENAB "High" during operation.

2)



R/L = L  
U/D = H



R/L = H  
U/D = H



R/L = L  
U/D = L



R/L = H  
U/D = L

## 7-2 . LED

No.	Symbol	Description
1	AN1	Anode 1
2	AN2	Anode 2
3	CA1	Cathode 1
4	CA2	Cathode 2

LCD side connector : PHR-4 (JST)

Recommended matching connector

: B4B-PH-SM4-TB (JST)

: B4B-PH-SM4-TB(LF)(SN) (JST) ... (RoHS Compliant)

: S4B-PH-SM4-TB (JST)

: S4B-PH-SM4-TB(LF)(SN) (JST) ... (RoHS Compliant)

Spec No. TQ3C-8EAFO-E1DEU50-00	Part No. TCG057VGLGA-G00	Page 8
-----------------------------------	-----------------------------	-----------

## 8. Input timing characteristics

### 8-1. Timing characteristics

Item		Symbol	Min	Typ	Max	Unit	Note
Clock	Frequency	1/Tc	22.66	25.18	27.69	MHz	
	Duty ratio	Tch/Tc	40	50	60	%	
Data	Set up time	Tds	5	-	-	ns	
	Hold time	Tdh	10	-	-	ns	
Horizontal sync. signal	Cycle	TH	30.0	31.8	-	μ s	
			770	800	850	clock	
	Pulse width	THp	2	96	200	clock	
Vertical sync. signal	Cycle	TV	515	525	560	line	
	Pulse width	TVp	2	-	34	line	
Horizontal display period		THd	640			clock	
Hsync,-Clock phase difference		THc	10	-	Tc-10	ns	
Hsync-Vsync. phase difference		TVh	2Tc	-	TH-THp-Tc	ns	
Vertical sync. signal start position		TVs	7			line	
Vertical display period		TVd	240			line	

- 1) In case of lower frequency, the deterioration of the display quality, flicker etc., may occur.

### 8-2. Horizontal display position


Item		Symbol	Min	Typ	Max	Unit	Note
Enable signal	Set up time	Tes	5	-	Tc-10	ns	
	Pulse width	Tep	2	640	TH-10	clock	
Hsync - Enable signal phase difference		The	44	-	104	clock	

- 1) When ENAB is fixed at "Low", the display starts from the data of C104(clock) as shown in 8-5.
- 2) The horizontal display position is determined by ENAB signal.


### 8-3. Vertical display position

- 1) The vertical display position (TVs) is 34th line.
- 2) ENAB signal is independent of vertical display position.

#### 8-4. Input Data Signals and Display position on the screen



#### 8-5. Input timing characteristics



- 1) When ENAB is fixed at "Low", the display starts from the data of C104(Clock).
- 2) The vertical display position(TVs) is fixed at 34th line.

Spec No. TQ3C-8EAFO-E1DEU50-00	Part No. TCG057VGLGA-G00	Page 10
-----------------------------------	-----------------------------	------------

## 9. Backlight characteristics

Item	Symbol	Min.	Typ.	Max.	Unit	Note
Forward current 1)	IF	-	60	-	mA	Ta=-20 ~ 70°C
Forward voltage 1)	VF	-	(9.5)	(11.2)	V	IF=60mA, Ta=-20
		-	(9.0)	(10.6)	V	IF=60mA, Ta=25
		-	(8.7)	(10.3)	V	IF=60mA, Ta=70
Operating life time 2), 3)	T	-	(70,000)	-	h	IF=60mA, Ta=25

- 1) For each "AN-CA"
- 2) When brightness decrease 50% of minimum brightness.  
The average life of a LED will decrease when the LCD is operating at higher temperatures.
- 3) Life time is estimated data.(Condition : IF=60mA, Ta=25 in chamber).
- 4) An input current below 15mA may reduce the brightness uniformity of the LED backlight.  
This is because the amount of light from each LED chip is different. Therefore, please evaluate carefully before finalizing the input current.

## 10. Lot number identification

The lot number shall be indicated on the back of the backlight case of each LCD.

TCG057VGLGA-G00 - □□ - □□ - □ MADE IN □□□□□  
 ↓ ↓ ↓ ↓  
 1 2 3 4 5

No1. - No5. above indicate  
 1. Year code  
 2. Month code  
 3. Date  
 4. Version Number  
 5. Country of origin (Japan or China)

Year	2010	2011	2012	2013	2014	2015
Code	0	1	2	3	4	5

Month	Jan.	Feb.	Mar.	Apr.	May	Jun.
Code	1	2	3	4	5	6

Month	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Code	7	8	9	X	Y	Z

Spec No.	Part No.	Page
TQ3C-8EAFO-E1DEU50-00	TCG057VGLGA-G00	11

## 11. Warranty

### 11-1. Incoming inspection

Please inspect the LCD within one month after your receipt.

### 11-2. Production warranty

Kyocera warrants its LCD's for a period of 12 months from the ship date. Kyocera shall, by mutual agreement, replace or re-work defective LCD's that are shown to be Kyocera's responsibility.

## 12. Precautions for use

### 12-1. Installation of the LCD

- 1) A transparent protection plate shall be added to protect the LCD and its polarizer
- 2) The LCD shall be installed so that there is no pressure on the LSI chips.
- 3) The LCD shall be installed flat, without twisting or bending.
- 4) A transparent protection sheet is attached to the polarizer. Please remove the protection film slowly before use, paying attention to static electricity.

### 12-2. Static electricity

- 1) Since CMOS ICs are mounted directly onto the LCD glass, protection from static electricity is required.
- 2) Workers should use body grounding. Operator should wear ground straps.

### 12-3. LCD operation

- 1) The LCD shall be operated within the limits specified. Operation at values outside of these limits may shorten life, and/or harm display images.

### 12-4. Storage

- 1) The LCD shall be stored within the temperature and humidity limits specified.  
Store in a dark area, and protect the LCD from direct sunlight or fluorescent light.
- 2) Always store the LCD so that it is free from external pressure onto it.

### 12-5. Usage

- 1) DO NOT store in a high humidity environment for extended periods. Polarizer degradation bubbles, and/or peeling off of the polarizer may result.
- 2) The front polarizer is easily scratched or damaged. Prevent touching it with any hard material, and from being pushed or rubbed.
- 3) The LCD screen may be cleaned by wiping the screen surface with a soft cloth or cotton pad using a little Ethanol.
- 4) Water may cause damage or discoloration of the polarizer. Clean condensation or moisture from any source immediately.
- 5) Always keep the LCD free from condensation during testing. Condensation may permanently spot or stain the polarizer.
- 6) Do not pull the LED lead wires and do not bend the root of the wires. Housing should be designed to protect LED lead wires from external stress.
- 7) Do not disassemble LCD because it will result in damage.

Spec No.	Part No.	Page
TQ3C-8EAF0-E1DEU50-00	TCG057VGLGA-G00	12

- 8) This Kyocera LCD has been specifically designed for use in general electronic devices, but not for use in a special environment such as usage in an active gas. Hence, when the LCD is supposed to be used in a special environment, evaluate the LCD thoroughly beforehand and do not expose the LCD to chemicals such as an active gas.
- 9) Please do not use solid-base image pattern for long hours because a temporary afterimage may appear. We recommend using screen saver etc. in cases where a solid-base image pattern must be used.
- 10) Liquid crystal may leak when the LCD is broken. Be careful not to let the fluid go into your eyes and mouth. In the case the fluid touches your body; rinse it off right away with water and soap.


### 13. Reliability test data

Test item	Test condition	Test time	Judgement
High temp. atmosphere	80°C	240h	Display function : (TBD) Display quality : (TBD) Current consumption : (TBD)
Low temp. atmosphere	-30°C	240h	Display function : (TBD) Display quality : (TBD) Current consumption : (TBD)
High temp. humidity atmosphere	40°C 90% RH	240h	Display function : (TBD) Display quality : (TBD) Current consumption : (TBD)
Temp. cycle	-30°C 0.5h R.T. 0.5h 80°C 0.5h	10cycles	Display function : (TBD) Display quality : (TBD) Current consumption : (TBD)
High temp. operation	70°C	500h	Display function : (TBD) Display quality : (TBD) Current consumption : (TBD)

- 1) Each test item uses a test LCD only once. The tested LCD is not used in any other tests.
- 2) The LCD is tested in circumstances in which there is no condensation.
- 3) The reliability test is not an out-going inspection.
- 4) The result of the reliability test is for your reference purpose only.


The reliability test is conducted only to examine the LCD's capability.

No	Description	Drawn	Checked	Checked	Approved




**DETAIL A (Dot Size)  
(NTS)**

Material 材質	Treatment 處理	Approved '10.03.15	Checked Checked '10.03.15	Checked '10.03.15	Drawn	Scale 1:1 (NTS)	Title TCG057VGLGA		Year-Month-Day '10.03.11	Size 2
Quantity 製作數	Description; 備考	RoHS	朝倉	朝倉	茶圓		Outline Dimensions	Drawing No. 121A8023800		




※取り付け例 (Installation guidance)



※裏面の押さえつけ可能領域以外 (押さえつけ禁止エリアを除く) を押さえると、取付構造によっては、表示ムラが発生する場合があります。  
しかしながら、GND接続等で押さえる必要がある場合は、25mm<sup>2</sup> (5mm×5mm)に対して、0.65kgf (6.4N)を目安として下さい。  
なお、上記値は、参考値であり、実際の取付構造により十分評価頂きますようお願いします。

(※ If area other than pressure available area on the rear side is pressured, there is a case that display variation is caused.  
However, when pressure is needed for GND connection or so, 0.65kgf (6.4N) per 25mm<sup>2</sup> (5mm×5mm) will be a referential figure.  
Above figure is reference only. Therefore, please evaluate well under the actual installation structure.)

## 参考 (for Reference)



取り付け方法  
(Installation of the LCD)

ケースにモジュールをはめ込み(x,y回り)、裏面からZ方向を固定する事が可能。  
(The LCD module shall be held in the X/Y direction by the housing, and in the Z direction using a backboard.)

斜線部の領域にて、下記の条件を満たし押さえることが望ましい。  
(To hold the LCD module in place, it shall be supported with pressure applied to the hatched areas indicated by the descriptions below.)

押さえつけ可能領域  
(Pressure may be applied in this area.)

押さえつけ可能領域面積 (裏面) : 2905.7mm<sup>2</sup>  
(Pressure may be applied in this area (Back side) : 2905.7mm<sup>2</sup>)  
参考全荷重 : 10kgf (98N)  
(Referential total load : 10kgf (98N))  
参考平均圧力 : 3.4gf/mm<sup>2</sup> (33.7kPa)  
(Referential average pressure : 3.4gf/mm<sup>2</sup> (33.7kPa))  
※上記値は参考値であり、実際の取付構造により十分評価頂きますようお願いします。  
(Above figure is reference only. Therefore, please evaluate well by the actual installation structure.)

押さえつけ不可領域  
(Pressure failure area.)

No	Description	Drawn	Checked	Checked	Approved

表面取り付け条件  
(Installation conditions (Front side))

1.広い範囲で均一に押さえることが望ましい  
(1. The LCD shall be uniformly supported over as wide an area as possible.)

裏面取り付け条件  
(Installation conditions (Back side))

1. PCBへの接触無きこと  
(1. Do not allow any foreign material to contact the PCB.)

2.モジュールがたわむこと無きよう押さえのこと  
(2. Do not allow the LCD module to bend or twist.)

3.広い範囲で均一に押さえることが望ましい  
(3. Support the LCD with uniform pressure over as wide an area as possible.)

注記 (Note)  
指定外公差 (Tolerance without indication) : ±0.5

Material 材質	Treatment 処理	Approved '10.04.20	Checked '10.04.20	Checked '10.04.20	Drawn 茶圓	Scale 1:1 (NTS)	Title TCG057VGLG* without T/P	KYOCERA Year-Month-Day '10.04.16	Size 2
Quantity 製作数	Description; 備考	RoHS					Module Installation		

Drawing No. 121A8025700

Spec No.	TQ3C-8EAF0-E2DEU50-00
Date	April 14, 2010

## **KYOCERA INSPECTION STANDARD**

**TYPE : TCG057VGLGA-G00**

KYOCERA CORPORATION  
KAGOSHIMA HAYATO PLANT  
LCD DIVISION

Original Issue Date	Designed by : Engineering dept.			Confirmed by : QA dept.	
	Prepared	Checked	Approved	Checked	Approved
April 14, 2010	S. Maezuru	<i>Y. Ikeda</i>	<i>D. Johnson</i>	J. Sakaguchi	<i>K. Saito</i>





Spec No. TQ3C-8EAF0-E2DEU50-00	Part No. TCG057VGLGA-G00	Page -
-----------------------------------	-----------------------------	-----------

### Revision record

Date	Designed by : Engineering dept.			Confirmed by : QA dept.	
	Prepared	Checked	Approved	Checked	Approved
Rev.No.	Date	Page	Descriptions		

**Visuals specification**

## 1) Note

Note											
General	<ol style="list-style-type: none"> <li>Customer identified anomalies not defined within this inspection standard shall be reviewed by Kyocera, and an additional standard shall be determined by mutual consent.</li> <li>This inspection standard about the image quality shall be applied to any defect within the active area and shall not be applicable to outside of the area.</li> <li>Inspection conditions           <table> <tr> <td>Luminance</td><td>: 500 Lux min.</td></tr> <tr> <td>Inspection distance</td><td>: 300 mm.</td></tr> <tr> <td>Temperature</td><td>: 25 ± 5</td></tr> <tr> <td>Direction</td><td>: Directly above</td></tr> </table> </li> </ol>			Luminance	: 500 Lux min.	Inspection distance	: 300 mm.	Temperature	: 25 ± 5	Direction	: Directly above
Luminance	: 500 Lux min.										
Inspection distance	: 300 mm.										
Temperature	: 25 ± 5										
Direction	: Directly above										
Definition of inspection item	Dot defect	Bright dot defect	<p>The dot is constantly “on” when power applied to the LCD, even when all “Black” data sent to the screen.</p> <p>Inspection tool: 5% Transparency neutral density filter.</p> <p>Count dot: If the dot is visible through the filter.</p> <p>Don’t count dot: If the dot is not visible through the filter.</p>  								
	Black dot defect		The dot is constantly “off” when power applied to the LCD, even when all “White” data sent to the screen.								
	Adjacent dot		Adjacent dot defect is defined as two or more bright dot defects or black dot defects.								
	External inspection	Bubble, Scratch, Foreign particle (Polarizer, Cell, Backlight)	Visible operating (all pixels “Black” or “White”) and non operating.								
		Appearance inspection	Does not satisfy the value at the spec.								
	Others	LED wires	Damaged to the LED wires, connector, pin, functional failure or appearance failure.								
	Definition of size	<p>Definition of circle size</p> 									
		<p>Definition of linear size</p> 									

Spec No.	Part No.	Page
TQ3C-8EAF0-E2DEU50-00	TCG057VGLGA-G00	2

## 2) Standard

Classification		Inspection item	Judgement standard	
Defect (in LCD glass)	Dot defect	Bright dot defect	Acceptable number : 4	Bright dot spacing : 5 mm or more
		Black dot defect	Acceptable number : 5	Black dot spacing : 5 mm or more
		2 dot join	Bright dot defect : 2	Black dot defect
		3 or more dots join	Acceptable number : 0	
	Others	Total dot defects	Acceptable number : 5 Max	
		White dot, Dark dot (Circle)	Size (mm)	Acceptable number
			d 0.2	(Neglected)
External inspection (Defect on Polarizer or between Polarizer and LCD glass)	Polarizer (Scratch)	0.2 < d 0.4	5	
		0.4 < d 0.5	3	
		0.5 < d	0	
		Width (mm)	Length (mm)	Acceptable number
		W 0.1	-	(Neglected)
	Polarizer (Bubble)	0.1 < W 0.3	L 5.0	(Neglected)
		5.0 < L	0	
		0.3 < W	-	0
		Size (mm)	Acceptable number	
		d 0.2	(Neglected)	
	Foreign particle ( Circular shape )	0.2 < d 0.3	5	
		0.3 < d 0.5	3	
		0.5 < d	0	
		Size (mm)	Acceptable number	
		d 0.2	(Neglected)	
	Foreign particle ( Linear shape ) Scratch	0.2 < d 0.4	5	
		0.4 < d 0.5	3	
		0.5 < d	0	
		Width (mm)	Length (mm)	Acceptable number
		W 0.03	-	(Neglected)
		0.03 < W 0.1	L 2.0	(Neglected)
		2.0 < L 4.0	3	
		4.0 < L	0	
		0.1 < W	-	(According to circular shape)