





NOTES:

- MATERIALS AND FINISHES: (PLATING THICKNESS IN MICRO-INCHES)
BODY - ZINC DIECAST, NICKEL PLATING
CONTACT - PHOSPHOR BRONZE, GOLD PLATING
INSULATOR - PTFE
- ELECTRICAL:
 - IMPEDANCE: 75 OHM
 - FREQUENCY RANGE: DC-4 GHz
 - VSWR(RETURN LOSS): 1.07+0.007 F(GHz).
 - DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.
- MECHANICAL:
 - DURABILITY: 500 CYCLES MIN.
 - TEMPERATURE RANGE: - 65°C to +165°C

B6252P2-NT3G-75

REVISIONS

DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	05/23/06	4619	GEFFERY

RECOMMENDED
MOUNTING HOLE

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

GLOBAL P/N

31-70336

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:

0.5 - 6mm	6 - 30mm	30 - 120mm	ANGLES
±0.1mm	±0.2mm	±0.3mm	±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE

131-6400-00

FINISH

PART NO.

DRAWN

GEFFERY

ENGINEER

APPROVED

CAD FILE

F:\DWG\B\6252P2\75\NT3GSZ

DATE

23-May-06

DATE

23-May-06

DATE

7/26/06

TITLE

BNC JACK RECEPTACLE
PCB MOUNT

ITEM NO. 016252AAAA1NA7F

CODE ID

74868

DWG SIZE

B

DRAWING NO.

B6252P2-NT3G-75

REV

A

Amphenol RF

Danbury, CT, USA

Tainan, Taiwan

Shenzhen, China

www.amphenolrf.com

SCALE: 1/1

SHEET 2 OF 2