




Printed: Sep 23, 2011

PRODUCT NUMBER	SERIES NAME	PITCH
20020011-CXXXXXXLF	02-350	3.50 mm





N = Number of poles

Dim A	NX3.5[.138]
Dim B	(N-1)X3.5[.138]
Dim C	NX3.5[.138]+9.6[.378]
Dim D	(N-1)X3.5[.138]+8.6[.339]


poles	Tolerance
2-4p	±0.10[.004]
5-7p	±0.15[.006]
8-12p	±0.20[.008]
13-18p	±0.25[.010]
19-24p	±0.30[.012]

mat'l. code		surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified	title TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK, W/FLANGE
E				angles X°±1°	sheet 2 of 5 size
				linear X.XX±0.1	20020011 A4
		dr	WENDY CHEN	051810	type CUSTOMER Drawing
		enr	JASON HSU	051810	
		chr	GARY HSIEH	051810	
		appd	JOSEPH HSIA	051810	
sheet index	revision sheet				

PRODUCT NUMBER	SERIES NAME	PITCH
20020011-DXXXXXXLF	02-381	3.81 mm



2p to 6p with wedge, above 7p
without wedge (including 7p)




N = Number of poles

Dim A	$N \times 3.81 [.150]$
Dim B	$(N-1) \times 3.81 [.150]$
Dim C	$N \times 3.81 [.150] + 9.6 [.378]$
Dim D	$(N-1) \times 3.81 [.150] + 9.0 [.354]$

poles	Tolerance
2-6P	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$
13-17p	$\pm 0.25 [.010]$
18-24p	$\pm 0.30 [.012]$

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
E				angles	$X \pm 0.5$	scale	TERMINAL BLOCK
				linear	$X.X \pm 0.3$		PLUGGABLE PLUG, BACK SIDE HOOK,
				$X^\circ \pm 1^\circ$	$X.XX \pm 0.1$		W/FLANGE
		dr	WENDY CHEN	051810			sheet 3 of 5
		enr	JASON HSU	051810			size
		chr	GARY HSIEH	051810			A4
		appd	JOSEPH HSIA	051810			20020011
sheet index	revision sheet						type
							CUSTOMER Drawing




PRODUCT NUMBER	SERIES NAME	PITCH
20020011-GXXXXXXLF	02-500	5.00 mm





N = Number of poles

Dim A	$N \times 5.0[.197] + 0.5[.020]$
Dim B	$(N-1) \times 5.0[.197]$
Dim C	$N \times 5.0[.197] + 10.0[.394]$
Dim D	$(N+1) \times 5.0[.197]$

poles	Tolerance
2-6p	$\pm 0.15[.006]$
7-12p	$\pm 0.20[.008]$
13-18p	$\pm 0.30[.012]$
19-24p	$\pm 0.40[.016]$







SECTION P-P



mat'l. code	surface ASME Y14.5	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title
E				TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK, W/FLANGE
				sheet 4 of 5 size
				20020011 A4
				type CUSTOMER Drawing
sheet index	revision sheet			

PRODUCT NUMBER	SERIES NAME	PITCH
20020011-HXXXXXXLF	02-508	5.08 mm




SECTION P-P

N = Number of poles

Dim A	$N \times 5.08 [.200] + 0.5 [.020]$
Dim B	$(N-1) \times 5.08 [.200]$
Dim C	$N \times 5.08 [.200] + 9.66 [.380]$
Dim D	$(N+1) \times 5.08 [.200]$

poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$
13-18p	$\pm 0.30 [.012]$
19-24p	$\pm 0.40 [.016]$



mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title	
E					angles	X.±0.5	TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK, W/FLANGE	
					linear	X.X±0.3		
					X'±1"	X.XX±0.1		
					dr	WENDY CHEN 051810		
					enr	JASON HSU 051810	sheet 5 of 5 size A4	
					chr	GARY HSIEH 051810		
					appd	JOSEPH HSIA 051810		
sheet index	revision	sheet					type	CUSTOMER Drawing

