

# 24" Rack Cases with Elastomer Shocks



AP3S-R908U24



Both lids can  
be removed and  
re-attached  
quickly and easily

AP3S-R916U24



Compound hinge  
technology allows  
270° door swing  
range even when  
cases are in a  
stacked position

AP3S-R910U24



**front to rear rail: 24" • Each lid 4.5" deep**

Ameripack's new Roto Shock Racks feature a (24" deep) roto molded tough shell with an integrally molded valance that eliminates the need for a metal valance on the outside of the case.

## FEATURES:

- Standard 19" rack width per EIA standards
- Standard rack depth front to rear rail is 24" and each lid is 4.5" deep
- Redesigned frame with threaded steel rails and aluminum cross components forming an "H" shaped rigid configuration
- Unique "plug" style lid sealing system. Lids penetrate the body with an approximate 1" molded-in protrusion that provides outstanding sealing and anti-shear properties
- Patent-pending compound hinge system allows the lids to swing out 270° & rest along the sides of the case or easily removed and reinstalled in seconds
- Front and rear doors are fitted with rubber gaskets for water resistant protection
- Recessed heavy-duty twist latches allow these cases to meet most ATA and military specifications
- Stacks securely with wheels on or off and this revolutionary design also allows for both lids to open completely while cases are stacked
- All sizes come standard with 8 each HM-245 elastomeric, high damping, wide temperature range shock mounts with a load range of 40 to 150 lbs.
- Additional or stiffer shock mounts may be ordered from the factory and are easily field-installed (call for details & availability)
- Standard high quality slide-in/out locking swivel 4" casters rated at 1,200 lbs.
- Automatic ambient pressure equalization valve (MIL-STD-648C)
- Black powder coated stainless steel key-lockable latches
- Comfortable, spring-loaded, rubber over-molded handles

Part #	Rack Units	Height
AP3S-RO6U24	6Space	10-1/2" High
AP3S-R908U24	8 Space	14" High
AP3S-R910U24	10 Space	17-1/2" High
AP3S-R912U24	12 Space	21" High
AP3S-R914U24	14 Space	24-1/2" High
AP3S-R916U24	16 Space	28" High

609-259-7004 • Fax: 609-259-8975

www.ameripack.com • E-Mail: sales@ameripack.com • 1-800-456-7963