

INTERCONNECTS

SERIES 351 • .100" GRID INTERCONNECT HEADERS • SINGLE ROW STRIPS




FIG. 1




FIG. 2





FIG. 3

- Series 351 interconnect header strips come in three lengths with .018" dia. pluggable solder tails at one end and .025" dia. pins at the other. Please see series:
351...003 uses pin #5503
351...004 uses pin #5504
351...005 uses pin #5505

- .018" pluggable solder tails are available at both ends. Please see series:
351...009 uses pin #5509
351...010 uses pin #5510
351...011 uses pin #5511
See pages 212 and 214 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 351...003	.018" / .025" Dia. Solder Tails
	351-10-1	-00-003000
	Specify number of pins	01-64
FIG. 2	Series 351...009	.018" / .018" Dia. Solder Tails
	351-10-1	-00-009000
	Specify number of pins	01-64
FIG. 3	Series 351...004	.018" / .025" Dia. Solder Tails
	351-10-1	-00-004000
	Specify number of pins	01-64
FIG. 3	Series 351...010	.018" / .018" Dia. Solder Tails
	351-10-1	-00-010000
	Specify number of pins	01-64
FIG. 3	Series 351...005	.018" / .025" Dia. Solder Tails
	351-10-1	-00-005000
	Specify number of pins	01-64
FIG. 3	Series 351...011	.018" / .018" Dia. Solder Tails
	351-10-1	-00-011000
	Specify number of pins	01-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Pin Plating		
10 10 μm Au		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[351-10-164-00-011000](#) [351-10-164-00-010000](#) [351-10-164-00-009000](#) [351-10-164-00-005000](#) [351-10-164-00-004000](#) [351-10-164-00-003000](#) [351-10-132-00-011000](#) [351-10-132-00-010000](#) [351-10-132-00-009000](#) [351-10-132-00-005000](#) [351-10-132-00-004000](#) [351-10-132-00-003000](#) [351-10-120-00-011000](#) [351-10-120-00-010000](#) [351-10-120-00-009000](#) [351-10-120-00-005000](#) [351-10-120-00-004000](#) [351-10-120-00-003000](#) [351-10-110-00-004000](#) [351-90-120-00-005000](#)