

- Evaluate
 - FAQ's
- Design a Solution
 - Application Notes
 - PDFLC Transceiv ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) Search Tips

Text Search: 'LCTRDGX'

Your search criteria matched only one product, shown below

LCTRDC-X



- Connectivity meets or exceeds TIA/EIA-568-B.3 and ISO/IEC 11801 performance requirements
- LC and SC connector housing and boot colors follow TIA/EIA -568-C.3 suggested color identification scheme
- Jacketed cable is compliant with NFPA 262 (OFNP) flame rating
- MTP* (12-fiber) connectors are FOCIS-5 compliant
- Insertion loss per mated pair: 0.50dB typical, 0.75dB max.
- Panduit proprietary MTP* polishing provides low insertion loss and high return loss, minimizing variability for improved channel link loss performance
- Traditional connectors (Panduit LC, SC, and ST) provide design flexibility throughout the data center
- Insertion loss per mated pair: 0.10dB typical, 0.30dB max. (multimode); 0.25dB typical, 0.50dB max. (singlemode)
- Factory terminated and 100% tested for insertion loss (test data supplied with each assembly); singlemode and 10Gig™ Multimode Hydra Cable Assemblies also tested for return loss

• TIA/EIA568-B.1-7 standards based polarity supports 10 Gb/s, multimode, and singlemode fiber types, and allows infrastructure backwards compatibility for component interchangeability and a lower cost of ownership

• 10Gig™ laser optimized fiber is tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters at 850nm

• Application specific designs available to tailor configuration, reach, and breakout construction to application requirements; for more information contact Panduit or visit www.panduit.com

Individual Staggered Hydra Cable Assemblies are available. Please see WW-FBCB38.

*MTP is a registered trademark of US Conec Ltd.

Part Number	LCTRDCX
Part Description	LC Transceiver Dust Cap helps manage the unused LC connectors and assists with cable management until those transceivers are installed.
Color	Red
Pricing Description	LC Transceiver Dust Cap
Min. Order UOM	PC
Min. Order Qty.	10
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	é

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.