






LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	REVISED PER EC 0512-0239-05	28OCT05	JDP	AMS




PC BOARD LAYOUT

1. DIMENSIONS IN BRACKETS ARE IN INCHES.
2. HOUSING MATERIAL: GLASS-FILLED POLYESTER, GRAY.
3. POST MATERIAL: PHOSPHOR BRONZE.
4. POST FINISH: DIN 41612 CLASS 3 IN CONTACT AREA.
TIN-LEAD PLATE ON POSTS.
5. POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA.
TIN-LEAD PLATE ON POSTS.
6. ACTION PIN POSTS REQUIRE 2.36 [.093] MIN THICK
PC BOARD. RECOMMENDED PC BOARD HOLES ARE ϕ 1.151 [.0453]
PLATED THROUGH WITH 0.02-0.08 [.001-.003] COPPER AND
0.008 [.0003] MIN TIN-LEAD PLATING. FINISHED HOLE
AFTER PLATING, ϕ 0.94-1.09 [.037-.043].
7. PART NUMBER, DATE CODE MARKED THIS APPROXIMATE AREA.
8. MARKING ON THIS SIDE.
9. POST FINISH: DIN 41612 CLASS 2 CONTACT AREA
TIN PLATE ON POSTS.



OBSELETE		1-16	X	X	X	48	7-650918-5
SUPERSEDED BY 650918-5		1-16	X	X	X	48	650918-9
		1-16	X	X	X	48	650918-5
	NOTES	POSITIONS LOADED	C	B	A	NO OF ROWS LOADED	ASSY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: BRINER 10MAY91 QDR: D.C. RUBENDALL 15MAY91 APVD: K. PARMER 15MAY91		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLG ± - 2 PLG ± - 3 PLG ± 0.13 [0.005] 4 PLG ± - 5 PLG ± - ANGLES ± -		NAME: ASSEMBLY, PIN, VERTICAL, EUROCARD, TYPE 1/2R 6.35 [250] PRESS-FIT POSTS	
MATERIAL: 		FINISH: 		SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO:	
				WEIGHT: - A1 00779 C-650918	
CUSTOMER DRAWING				SCALE: 5:1 SHEET 1 OF 1 REV 1	