




REV.	DATE	ECR NO.	DESCRIPTION
NC	08/17/02	—	INITIAL RELEASE
A	03/16/09	—	REVISE PART DESCRIPTION, ADD NOTE 1.



RECOMMENDED CABLE
STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .255" [6.48]

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex UHF CRIMP PLUG (FOR RG-59/U CABLE)					
8						DRAWN	GRS						03/16/09
7						CHECKED							
6						ISSUED							
5						SHEET	1 OF 1						
4	FERRULE	COPPER	NICKEL	1					PART NO.	182101			
3	CONTACT PIN	BER. COPPER	GOLD	1					DWG. NO.	182101.DWG	REV. A	SIZE A	SCALE NA
2	INSULATOR	PHENOLIC	YELLOW	1									
1	BODY/SHELL	BRASS	NICKEL	1									
	DESCRIPTION	MATERIAL	FINISH	QTY					CAD FILE				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[182101](#)