




CONTACT DIMENSIONS



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

① MATERIAL HOUSING : GREY GLASS FILLED POLYESTER
UL-RATING V0
CONTACT : PHOSPHORBRONZE

② GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN.
AND ACTION PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

③ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.

④ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.

⑤ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.

⑥ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III UNCONTROLLED ENVIRONMENT APPLICATIONS.

⑦ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.

⑧ CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.

⑨ CONNECTOR MARKED WITH PARTNUMBER AND DATECODE

⑩ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.

⑪ HOLES IN ROW f FOR POSSIBLE FUTURE USE OF GROUND RETURN SHIELDS. (NOT YET TOOLED)

⑫ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

⑬ 0.76µm MIN. GOLD PLATING AT MATING SURFACE

12	OBsolete	N	2 3 ¹³	3-5106014-0
12	OBsolete	Y 7	2 6	1-5106014-9
		N	2 3	1-5106014-1 8
12	OBsolete	Y 7	2 5	-5106014-9
12	OBsolete	N	2 4	-5106014-4
		N	2 3	5106014-1
		CONSERVATION TREATMENT	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.N.KIRAN	12AUG2004	 TE Connectivity	
		CHK B.MOOIJ	23SEP2004		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD B.MOOIJ	23SEP2004	NAME	
mm		PRODUCT SPEC		Z-PACK 2mm HM TYPE B	
	±0.2	108-19082		125 POS. RIGHT ANGLE MALE CONNECTOR ASSEMBLY	
		APPLICATION SPEC		SIZE	CAGE CODE
		114-19029			DRAWING NO
MATERIAL	FINISH	WEIGHT		A2	00779
-	-	-		C	5106014
CUSTOMER DRAWING			SCALE	SHEET	REV
			5:1	1 of 1	F