

Coaxial DC Block

0.01 to 18 GHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Max. DC input voltage	50V

Features

- broadband performance
- low insertion loss
- rugged unibody construction
- off-the-shelf availability


Applications

- test and measurement instrumentation
- communication systems
- defense systems



CASE STYLE: FF888
CONNECTOR: SMA (F) - SMA (M)
PRICE: \$21.95 ea.
QTY. (1-9)

Outline Drawing



B-OVERALL BODY DIMENSION
* MAX
** ACROSS FLATS

Outline Dimensions (inch mm)



B	D	E	wt.
.46	1.18	.31	grams
11.68	29.97	7.87	7.0

Electrical Specifications at 25°C

FREQUENCY (GHz)	INSERTION LOSS (dB)		RETURN LOSS (dB)	
	Typ.	Max.	Typ.	Min.
0.01-0.1	0.02	0.2	26	20
0.1-1.0	0.07	0.3	36	20
1.0-4.0	0.15	0.5	24	20
4.0-8.0	0.38	1.0	18	15
8.0-18	1.00	—	12	—

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	
		MALE	FEMALE
10.00	0.05	28.49	28.48
50.00	0.03	45.13	45.06
100.00	0.03	50.04	50.34
300.00	0.05	39.11	39.36
500.00	0.07	35.50	35.89
700.00	0.11	34.05	34.48
900.00	0.10	32.59	33.09
1000.00	0.10	31.87	32.59
2000.00	0.10	28.84	28.45
3000.00	0.12	26.71	25.78
4000.00	0.20	24.84	24.46
5000.00	0.28	22.08	23.35
6000.00	0.35	19.95	21.73
7000.00	0.41	20.10	20.67
8000.00	0.47	17.98	18.83
10000.00	0.64	15.04	15.60
12000.00	0.80	14.59	12.85
14000.00	0.99	12.82	12.36
16000.00	1.08	13.07	12.06
18000.00	1.03	16.78	12.60



Mini-Circuits®

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

ISO 9001 CERTIFIED

INTERNET <http://www.minicircuits.com>

REV. A
M86026
BLK-18
EE-9517/2
URJ/LC/CP
030317