

			REVISIONS																																																
			REV	DESCRIPTION	DATE	APPROVED																																													
			01 ₀	RELEASED	KYLE 10/22/97	PCW																																													
			B	REVISED PER ECN 0U20-0262-01	GV 1/6/03	JGH																																													
<table><tr><td>ELECTRICAL</td><td>MECHANICAL</td><td>ENVIRONMENTAL</td></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions MIL-STD-348A</td><td>TEMPERATURE RATING -65° TO +125°C</td></tr><tr><td>Frequency Range (GHz) DC to 18</td><td>Fig. 321-1</td><td>Vibration MIL-STD-202, Method 204, Condition D</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 335</td><td>Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5</td><td>Shock MIL-STD-202, Method 213, Condition I</td></tr><tr><td>VSWR 1.07+.01f(GHz) DC to 18 GHz</td><td>Center Contact Captivation</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B</td></tr><tr><td>Insertion Loss (dB MAX) .03x√f(GHz)</td><td>Axial (Lbs) 6.0</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>RF Leakage (dB MIN) (Fully Mated) -(60-f(GHz))</td><td>Weight (Grams) TBD</td><td>Corrosion - MIL-STD-202, Method 101, Condition B</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 250</td><td></td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000</td><td></td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0</td><td></td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670</td><td></td><td></td></tr><tr><td>I.R.(Megohms MIN) 10000</td><td></td><td></td></tr></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A	TEMPERATURE RATING -65° TO +125°C	Frequency Range (GHz) DC to 18	Fig. 321-1	Vibration MIL-STD-202, Method 204, Condition D	Volt Rating (VRMS MAX) @ Sea Level 335	Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5	Shock MIL-STD-202, Method 213, Condition I	VSWR 1.07+.01f(GHz) DC to 18 GHz	Center Contact Captivation	Thermal Shock MIL-STD-202, Method 107, Condition B	Insertion Loss (dB MAX) .03x√f(GHz)	Axial (Lbs) 6.0	Moisture Resistance MIL-STD-202, Method 106	RF Leakage (dB MIN) (Fully Mated) -(60-f(GHz))	Weight (Grams) TBD	Corrosion - MIL-STD-202, Method 101, Condition B	Corona, 70,000 Ft (VRMS MIN) 250			Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000			Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0			RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670			I.R.(Megohms MIN) 10000			<table><tr><td>HOUSING</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>PASSIVATE PER QQ-P-35</td></tr><tr><td>DIELECTRIC</td><td>PTFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>O-RING</td><td>FLOUROSILICONE PER MIL-R-25988, CLASS I, TYPE I.</td><td>N/A</td></tr></table>	HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	O-RING	FLOUROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																	
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A	TEMPERATURE RATING -65° TO +125°C																																																	
Frequency Range (GHz) DC to 18	Fig. 321-1	Vibration MIL-STD-202, Method 204, Condition D																																																	
Volt Rating (VRMS MAX) @ Sea Level 335	Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5	Shock MIL-STD-202, Method 213, Condition I																																																	
VSWR 1.07+.01f(GHz) DC to 18 GHz	Center Contact Captivation	Thermal Shock MIL-STD-202, Method 107, Condition B																																																	
Insertion Loss (dB MAX) .03x√f(GHz)	Axial (Lbs) 6.0	Moisture Resistance MIL-STD-202, Method 106																																																	
RF Leakage (dB MIN) (Fully Mated) -(60-f(GHz))	Weight (Grams) TBD	Corrosion - MIL-STD-202, Method 101, Condition B																																																	
Corona, 70,000 Ft (VRMS MIN) 250																																																			
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000																																																			
Contact Resistance (Milliohms MAX) Center Contact 2.0 Outer Contact 2.0																																																			
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670																																																			
I.R.(Megohms MIN) 10000																																																			
HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35																																																	
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A																																																	
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204																																																	
O-RING	FLOUROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A																																																	
<table><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr><tr><td>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON</td><td>FRAC. DEC. ANGLES</td><td></td></tr><tr><td>± 1/64 ± .005 ± 1°</td><td></td><td></td></tr><tr><td>These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td>USE ASS'Y PROCEDURE</td><td></td></tr><tr><td></td><td>NO. A.P. N/A</td><td></td></tr></table>			COMPONENT	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	FRAC. DEC. ANGLES		± 1/64 ± .005 ± 1°			These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE			NO. A.P. N/A		<table><tr><td>DRAWN BY PCW</td><td>DATE 9/11/97</td><td rowspan="3">AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>CHECKED BY</td><td></td></tr><tr><td>APPR'D BY PCW</td><td>10/2/97</td></tr></table>	DRAWN BY PCW	DATE 9/11/97	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	CHECKED BY		APPR'D BY PCW	10/2/97																										
COMPONENT	MATERIAL	FINISH																																																	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	FRAC. DEC. ANGLES																																																		
± 1/64 ± .005 ± 1°																																																			
These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE																																																		
	NO. A.P. N/A																																																		
DRAWN BY PCW	DATE 9/11/97	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																	
CHECKED BY																																																			
APPR'D BY PCW	10/2/97																																																		
<table><tr><td colspan="2">TITLE</td><td>REV</td></tr><tr><td colspan="2">DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL</td><td>01₀</td></tr><tr><td>SIZE B</td><td>CODE IDENT NO. 26805</td><td></td></tr><tr><td colspan="2">SCALE 4:1</td><td>SHEET 1 OF 1</td></tr></table>			TITLE		REV	DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL		01 ₀	SIZE B	CODE IDENT NO. 26805		SCALE 4:1		SHEET 1 OF 1																																					
TITLE		REV																																																	
DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE STRAIGHT TERMINAL		01 ₀																																																	
SIZE B	CODE IDENT NO. 26805																																																		
SCALE 4:1		SHEET 1 OF 1																																																	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4551-5054-02](#)