



PRODUCT NUMBER
SEE TABLE, SHEET 5

A



FCI

Copyright FCI.

D

rev	ecn no	dr	date
A	V05-0461	LRJ	2006-02-24
B	V06-0209	LRJ	2006-03-01
C	V06-0531	SCS	2006-06-07
D	S06-0374	DG	2006-12-21
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com				surface 3.2 ASME Y14.5		tolerance std ASME Y14.5 -		projection	MM
Dr	D. BUSH	2004-10-01		ANGULAR	LINEAR	0.X	±	size	Scale
Eng	S. MINICH	2004-10-01				0.XX	±		5:2
Chr	C. H. TAN	2006-12-21		0°	±°	0.XXX	±	ECN	***
Appr	JOEY NG	2006-12-21	Product family AirMax VS					Spec ref	

FCI AirMax VS R/A HEADER ASSY
PRESS-FIT, 72 POS, 16MM

catalog no - CUSTOMER sheet 1 of 5

dwg no 10045266 Rev. D

DESCRIPTION	DIM A	DIM B	DIM C
2-16MM MODULES PLACED END-TO-END	2.00	15.90 2X	16.00
1-16MM MODULE & 1-18MM MODULE PLACED END-TO-END	3.00	15.90 1X & 17.90 1X	17.00

A


A

B

B

C

C



Copyright FCI



16 AirMax VS R/A HEADER ASSY
PRESS-FIT, 72 POS, 16MM
catalog no

dwg no 10045266
Rev. D
- CUSTOMER

sheet 2 of 5

DESCRIPTION	DIM D	DIM E	DIM F
2-16MM MODULES PLACED END-TO-END	2.00	15.90 2X	16.00
1-16MM MODULE & 1-18MM MODULE PLACED END-TO-END	3.00	15.90 1X & 17.90 1X	17.00

A

A

B


B

C

C

D

D



RECOMMENDED PCB LAYOUT
FOR SINGLE ENDED APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6 & 7




AirMax VS R/A HEADER ASSY
PRESS-FIT, 72 POS, 16MM
catalog no

dwg no 10045266
Rev. D
- CUSTOMER

sheet 3 of 5

FCI

Copyright FCI.



REV F - 2006-04-17
AirMax VS R/A HEADER ASSY
PRESS-FIT, 72 POS, 16MM
catalog no

no 10045266 Rev. D
dwg no - CUSTOMER sheet 4 of 5

PART NUMBER	PRESS-FIT TAIL PLATING TYPE	SHORT DETECT CONTACT
10045266-101	TIN/LEAD ALLOY OVER NICKEL	NO
10045266-101LF	TIN OVER NICKEL (LEAD FREE)	
10045266-111	TIN/LEAD ALLOY OVER NICKEL	YES (SEE NOTE 13)
10045266-111LF	TIN OVER NICKEL (LEAD FREE)	

NOTES:

1. CONNECTOR MATERIALS:

HOUSING & RETAINER: HIGH TEMP THERMOPLASTIC, NATURAL, UL94V-0
 IMLA PLASTIC: HIGH TEMP THERMOPLASTIC, BLACK, UL94V-0
 CONTACT: COPPER ALLOY

2. CONTACT PLATING:

SEPARABLE INTERFACE:

PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-239 INCLUDING TELCORDIA GR-1217-CORE (NOVEMBER 1995) CENTRAL OFFICE TEST SEQUENCE

PRESS-FIT TAILS: SEE TABLE

3. PRODUCT SPECIFICATION: GS-12-239

4. APPLICATION SPECIFICATION: GS-20-035


5. PRODUCT MARKING, (PART NUMBER & LOT CODE), ON THIS SURFACE

6. REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING PCB LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES

7. POSITIONS F OF ODD NUMBERED COLUMNS AND POSITIONS G OF EVEN NUMBERED COLUMNS CORRESPOND TO EARLY MATE HEADER PINS

8. THERE IS NO GROUND BUSSING WITHIN THE CONNECTOR SYSTEM

9. REFER TO CUSTOMER DRAWING 10045979 FOR INFORMATION ON PCB HOLE DIAMETERS AND PLATING OPTIONS.



10. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

11. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

12. PACKAGING MEETS GS-14-920 LEAD FREE LABELING SPECIFICATION.

13. MATING PIN E4 HAS 0.5mm LESS NOMINAL WIPE THAN THE SHORTEST SIGNAL PIN.

FCI	1e AirMax VS R/A HEADER ASSY	dwg no	10045266	Rev. D
	1- PRESS-FIT, 72 POS, 16MM	catalog no	-	CUSTOMER
				sheet 5 of 5