


3M™ TWIN AXIAL CABLE, SL8800 SERIES



- NOTES
- DIMENSIONS ARE IN MILLIMETERS.
 - PHYSICAL:
INSULATION MATERIAL: POLYOLEFIN
COLOR: SILVER
MARKING: NONE
 - ELECTRICAL:
IMPEDANCE: 100 ± 5 OHMS
 - PRODUCT SPECIFICATION: # PS-0079
 - THIS UNIQUE CABLE CONSTRUCTION HAS A THIN ALUMINUM INNER LAYER EXPOSED AT EACH EDGE. USERS SHOULD ASSESS WHETHER THE EXPOSED EDGE PRESENTS A SHORTING RISK IN THEIR SPECIFIC APPLICATION. INSULATING TAPE MAY BE APPLIED AT THE CABLE ASSEMBLY LEVEL, AS NEEDED TO COVER THIS EXPOSED EDGE IN RISK AREAS.
 - REGULATORY INFORMATION:
ROHS COMPLIANT. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "ROHS COMPLIANCE" SECTION OF WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY)

UL FILE NUMBER: E42769
 - FOIL-STRIPPING PROFILED BLADE DESIGN
DRAWING: 12-2678-5168-6

PLATING OPTION	PART NUMBER
Ag	SL8802/08-201N5-00
Sn	SL8802/08-211N5-00

B	32780	MAR 04,2011	LDS	DD
A	30167	AUG 09,2010	ML	ML
REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
DRFT	L SCHMIDT	DATE MAR 04,2011	MFG	DATE
CHKD		DATE	APPVL	DATE
© 3M COPYRIGHT 2011				
This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.				
TITLE				
3M RIBBON TWIN AXIAL CABLE, SL8802/08, 4 PAIR, 2 DRAINS				
CAGE NUMBER	SIZE	DRAWING NO.	REV.	
125	C	78-5100-2361-3	B	
MODEL			DET. LISTS	YES ☒ NO ☐
			SHT	1 OF 3