


HONEYWELL PART NUMBER
21SX83-H340
PRODUCT CODE VDM5750

REV	DOCUMENT	CHANGED BY	CHECK
6	0038450	PK 03JUN08	ASD



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 THIS IS A CUSTOMER REQUIREMENT AND MUST BE MET
 - 4 - SWITCH WILL WITHSTAND TEMPERATURE OF 185°F

RELEASE NO. PR-14290-T

REPLACES

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH	DRAWN	SPK	21FEB08	Honeywell			
OPERATING FORCE - - - 5 OZ MAX		CONTACT ARRANGEMENT SPDT				TOLERANCES UNLESS NOTED:	CHECK	RJ	21FEB08				
RELEASE FORCE - - - - 1 OZ MIN		28 VOLTS DC RATING 115 VOLTS AC, 60 CPS				NO PLACE X ±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE		
DIFFERENTIAL TRAVEL - - - .005 MAX		SEA LEVEL 50,000 FT SEA LEVEL				ONE PLACE .X ±					SWITCH - BASIC		
OVERTRAVEL - - - - - .004 MIN		INDUCTIVE 4 AMP 2.5 AMP 7 AMP				TWO PLACE .XX ±					SIZE	TYPE	DRAWING NAME
		RESISTIVE 7 AMP 4 AMP 7 AMP				THREE PLACE .XXX ±					B	I	21SX83-H340
		LAMP 2.5 AMP 2.5 AMP 2 AMP				FOUR PLACE .XXXX ±	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				REV		
		APPROVALS KEMA, CE 7A 250 V ~ T125 5E4 UL, CSA 7A 250 VAC				ANGLES ±					6		
						THIRD ANGLE PROJECTION	RASTER				SCALE	-	WEIGHT:.003 LB MAX
											SHEET 1 OF 1		