


PRODUCT NUMBER	SIZE	LATCHING AVAILABILITY	MISSING PIN POSITIONS
71918-X06(B)LF	2x3	0/1/2	
71918-X08(B)LF	2x4	0/1/2	
71918-X10(B)LF	2x5	0/1/2	
71918-X14(B)LF	2x7	0/1/2	
71918-X16(B)LF	2x8	0/1/2	
71918-X18(B)LF	2x9	0/1/2	
71918-X20(B)LF	2x10	0/1/2	
71918-X26(B)LF	2x13	0/1/2	
71918-X27(B)LF	2x13	0/1/2	PIN 21 & 22
71918-X28(B)LF	2x13	0/1/2	PIN 5 to 12
71918-X30(B)LF	2x15	0/1/2	
71918-X34(B)LF	2x17	0/1/2	
71918-X35(B)LF	2x17	0/1/2	PIN 2 & 3
71918-X40(B)LF	2x20	0/1/2	
71918-X44(B)LF	2x22	0/1/2	
71918-X50(B)LF	2x25	0/1/2	
71918-X51(B)LF	2x25	0/1/2	PIN 39 to 46
71918-X60(B)LF	2x30	0/1/2	
71918-X64(B)LF	2x32	0/1/2	



PLATING :

- 0.76µm GOLD/GXT
(PdNi WITH GOLD FLASH) ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
UNDERPLATE : 1.27µm Ni MIN

LATCHING FEATURES :



PIN POSITION INDICATION FOR POLARIZED VERSIONS



WHEN THE CONNECTORS NEED TO BE FIXED ON THE PCB'S
THE STAINLESS SCREWS REF TC POZI DIN7981 Ø2.9 X 6.5MM
TO BE USED

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr	ecn no	dr	date	tolerances unless otherwise specified					scale 2:1	title SHR.EL.HEADER STR DR TMT			
R	F07-0195	LMU	07.05.25	angles	linear	.X ±0.3							
S	F08-0146	YOV	08.04.11			.XX ±0.15							
T	F12-0011	LMU	12.02.06			.XXX ±0.05							
U	F12-0838	LMU	12.12.06	dr	D.LE		01.01.24		dwg no		sheet 2 of - size		
V	B-16776	LMU	14.01.23	engr	JM.C		01.01.24		71918		A3		
W	B-19091	LMU	14.10.16	chr	JF.N		01.01.24		type CUSTOMER Drawing				
X	B-20412	BVE	15.03.10	appd	JM.C		01.01.24						
sheet index		revision sheet											