






Electrical Properties:

Frequency Range:	902~928 MHz
Impedance:	50Ω nominal
VSWR:	<2.0:1
Gain:	*2.0 dBi
Radiation:	Omni
Polarization:	Vertical
Wave:	Half Wave Dipole

Mechanical Properties:







Material:	
Whip:	Polyurethane(Black)
Swivel Mechanism:	Polycarbonate(Black)
Connector:	Brass with black chrome plating
Operation Temp.:	-20°C to +65°C
Storage Temp.:	-30°C to +75°C

This is a RoHS compliant product.

Rev. Date
04/23/13

TITLE	900 MHz ISM Band Swivel Antenna - 467 model		Rev. Date	SHEET
			04/23/13	1 of 2
UNIT	DWG. NO.	S467XX - 915S		
in.(mm)				
SCALE				
none				

NEARSON



Series Part Numbers

Connector Code -XX-	Description	P / N
AM	SMA Plug	S467AM-915S
AH	SMA Plug Reverse Polarity	S467AH-915S
TC	TNC	S467TC-915S
TR	TNC Plug Reverse Polarity	S467TR-915S
BC	BNC	S467BC-915S
BR	BNC Plug Reverse Polarity	S467BR-915S

Connector Interface



SMA Plug
(AM)



SMA Plug Reverse Polarity
(AH)



TNC Plug
(TC)



TNC Plug Reverse Polarity
(TR)



BNC Plug
(BC)



BNC Plug Reverse Polarity
(BR)

TITLE		900 MHz ISM Band Swivel Antenna - 467 model		Rev. Date	SHEET
				04/23/13	2 of 2
UNIT	DWG. NO.	S467XX - 915S			
in.(mm)					
SCALE					
none					
NEARSON					