

Ba9 series

Bayonet cap based LED's •
single or multichip LED illumination



DISTINCTIVE FEATURES

Bayonet Cap based LED for bulb replacement

Operating & Storage Temperature Range: -20 °C to +70 °C
(-4 °F to +158 °F)

6 VDC to 230 VAC 9 to 17 mA, mcd range from 105 to 2,070
dependent on version



MATERIALS

- Body : Polycarbonate
- Base : Nickel plated brass



BUILD YOUR PART NUMBER

BA9 SINGLE CHIP

BA9

SERIES

TYPE

S Single Chip

COLOR

R Red
G Green
Y Yellow

B Blue
W White

VOLTAGE & CURRENT AC/DC

6A	6 V_9/17 mA	48A	48 V_9/8 mA
12A	12 V_9/17 mA	130A	130 VAC_9 mA
24A	24 V_9/17 mA	230A	230 VAC_9 mA
28A	28 V_9/17 mA		

For other voltage options please contact APEM

LUMINOUS INTENSITY

Color	Voltage			
	6 V, 12 V, 24 V & 28 V	48 V	130 VAC	230 VAC
R - Red	1,750 mcd	990 mcd	685 mcd	375 mcd
G - Green	1,610 mcd	920 mcd	570 mcd	345 mcd
Y - Yellow	630 mcd	360 mcd	225 mcd	135 mcd
B - Blue	490 mcd	280 mcd	175 mcd	105 mcd
W - White	2,070 mcd	1,180 mcd	710 mcd	470 mcd

The company reserves the right to change specifications without notice.



Ba9 series

Bayonet cap based LED's •
single or multichip LED illumination

BUILD YOUR PART NUMBER

BA9 MULTICHIP

BA9

SERIES

TYPE

COLOR

VOLTAGE & CURRENT AC/DC

C

Multi Chip

R

Red

G

Green

Y

Yellow

B

Blue

W

White

24A

24 V - 9/17 mA

28A

28 V - 9/17 mA

48A

48 V - 8 mA

130A

130 VAC - 5 mA

230A

230 VAC - 3 mA

For other voltage options please contact APEM

LUMINOUS INTENSITY

Color	Voltage			
	24 V & 28 V	48 V	130 VAC	230 VAC
R - Red	3 x 1,750 mcd	3 x 990 mcd	3 x 685 mcd	3 x 375 mcd
G - Green	3 x 1,610 mcd	3 x 920 mcd	3 x 570 mcd	3 x 345 mcd
Y - Yellow	3 x 630 mcd	3 x 360 mcd	3 x 225 mcd	3 x 135 mcd
B - Blue	3 x 490 mcd	3 x 280 mcd	3 x 175 mcd	3 x 105 mcd
W - White	3 x 2,070 mcd	3 x 1,180 mcd	3 x 710 mcd	3 x 470 mcd

BA9 - SINGLE CHIP WHITE

