


SUBMINIATURE Switch Modules

E61-E63 Series



Features

- 3 Contact Ratings
- Long life coil spring mechanism
- Choice of actuator
- Four terminal types
- RoHS compliant

Electrical Ratings and Operating Life

Switch Series	According to UL 1054	
	Nominal Load	Electrical Life at Rated Load
E61	5A 125/250 VAC	6000
E62	10.1A 125/250 VAC; 1/4HP 125VAC	6000
E63	0.1A 125VAC	6000

Technical Specifications

Temperature Rating:	-40°C to 85°C
Flammability Rating	UL94HB
Mounting:	Recommended screw: #2-56 round head Recommended torque: 2 inch lbs. max
UL File Number:	E23301


Specifications subject to change

Material Specifications

Case:	Thermoplastic
Actuating Button:	Thermoplastic Acetal
Terminal:	Silver Plated Commercial Bronze
Moving Blade:	Beryllium Copper
Spring:	Stainless Steel
Contacts:	E61, E62: Fine Silver E63: Gold Crosspoint
Auxiliary Actuator:	Cold Rolled Steel (Nickel-Plated)



Dimensions inches




0.470 +/- 0.020 (11.934 +/- 0.51)
0.672 +/- 0.020 (17.07 +/- 0.51)
0.875 +/- 0.020 (22.23 +/- 0.51)
1.066 +/- 0.020 (27.58 +/- 0.51)

0.063 (1.60) Ø (3)

0.405 (10.29)

0.237 (6.02) — PCB Terminals Straight Down Only —





Technical drawing showing a shaft with a keyway and a shaft-hub assembly. The shaft diameter is $\varnothing .182 \pm .003$ and the shaft length is $0.125"$.



SUBMINIATURE Switch Modules

E61-E63 Series

Terminals:

Terminal Type	Dimensions	Actuator Position	Part Number Suffix (with straight lever)			
			2PDT	3PDT	4PDT	5PDT
QC (Quick Connect) 0.093" (2.36)**		Standard Ratio	-02HM	-03HM	-04HM	-05HM
		High Ratio	-52HM	-53HM	-54HM	-55HM
Short Solder 0.143" x 0.125" (3.63mm x 3.18mm)		Standard Ratio	-12HM	-13HM	-14HM	-15HM
		High Ratio	-62HM	-63HM	-64HM	-65HM
QC (Quick Connect) 0.110" (2.794mm) ***		Standard Ratio	-32HM	-33HM	-34HM	-35HM
		High Ratio	-82HM	-83HM	-84HM	-85HM
PCB 0.049" x 0.176" (1.25mm x 4.47mm)		Standard Ratio	Consult Factory			
		High Ratio	Consult Factory			

Consult factory for switch part numbers if ordering pcb terminals

Terminal Mating Connectors:

** 0.093" QC terminals mate with AMP part number 60432-1

*** 0.110" QC terminals mate with AMP part number 42068-1

Switch Characteristics

- Consult factory for switch availability and characteristics.

Ordering Information

1. Select the contact rating prefix you need (E61-E63).
2. Combine the prefix with the corresponding terminal configuration. For example part number E63-02HM will provide you with a gold crosspoint subminiature switch module with 0.093" QC terminals and a straight lever with a 0.396" actuation length.

Contact

Call, fax or visit our
Website for more information.

ZF Electronics Corporation
11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262.942.6500
Web: www.cherrycorp.com
Email: cep_sales@zf.com
Fax: 262.942.6566

The manufacturer accepts no
liability for errors or non-
availability, and reserves the
right to change specifications
without prior notice.

Technical data relates to
product specifications only.
Features may differ from those
described. Only drawings
combined with product
specifications shall be deemed
binding.

© 2007 ZF Electronics
Corporation

