

T-CONNECTOR

Type NT

Tubing Run—Tubing Tap

A high copper alloy Multigrip type T-Connector for tubing run and tap. Slotted between bolts to provide independent high pressure areas of contact. High strength Durium oval shank bolts are readily installed with only one wrench. Finished to provide minimum contact resistance.

Listed by C.S.A.




Fig. 2

Fig. 1

Type NT

For use on ALUMINUM conductors, add -W to catalog number

IPS		CATALOG NUMBER	APPROX. SHIP. WT. IN LBS.	FIG. NO.	DIMENSIONS IN INCHES								
RUN	TAP				A	AA	B	H (MAX.)	J	L	W	BB	Y
1/4"	1/4"	NT1111	1.0	1	.540	.540	1 3/8	1 1/8	3/8	3 3/8	1 1/8	1 3/8	2 1/4
3/8"	3/8"	NT1211	1.1	1	.675	.540	1 3/8	1 1/8	3/8	3 3/8	1 1/8	1 3/8	2 3/8
1/2"	1/2"	NT1212	1.2	1	.675	.675	1 3/8	1 1/8	3/8	3 3/8	2 1/8	1 3/8	2 5/8
1/2"	1/4"	NT1311	1.2	1	.840	.540	1 3/8	1 1/8	3/8	3 1/2	1 1/8	1 3/8	2 3/8
1/2"	3/8"	NT1312	1.3	1	.840	.675	1 3/8	1 1/8	3/8	3 1/2	2 1/8	1 3/8	2 3/8
1/2"	1/2"	NT1313	2.1	2	.840	.840	2	1 1/8	3/8	3 1/2	2 1/8	2	2 1/8
3/4"	3/4"	NT1412	1.3	1	1.050	.675	1 3/8	1 1/8	3/8	3 1/2	2 1/8	1 3/8	2 7/8
3/4"	1/2"	NT1413	2.1	2	1.050	.840	2	1 1/8	3/8	4 1/8	2 1/8	2	2 7/8
3/4"	3/4"	NT1414	2.3	2	1.050	1.050	2	1 1/8	3/8	4 1/8	2 1/8	2	2 7/8
1"	3/8"	NT1512	1.3	1	1.315	.675	1 3/8	2	3/8	3 1/2	2 1/8	1 3/8	2 5/8
1"	1/2"	NT1513	2.3	2	1.315	.840	2	2 1/8	3/8	4 3/8	2 1/8	2	3
1"	3/4"	NT1514	2.5	2	1.315	1.050	2	2 1/8	3/8	4 3/8	2 1/8	2	3
1"	1"	NT1515	2.7	2	1.315	1.315	2	2 1/8	3/8	4 3/8	2 1/8	2	3 1/8
1 1/4"	1/2"	NT1613	2.6	2	1.660	.840	2	2 3/8	3/8	4 3/8	2 1/8	2	3 1/8
1 1/4"	3/4"	NT1614	2.7	2	1.660	1.050	2	2 3/8	3/8	4 3/8	2 1/8	2	3 1/8
1 1/4"	1"	NT1615	3.2	2	1.660	1.315	2	2 3/8	3/8	4 3/8	2 1/8	2	3 1/8
1 1/4"	1 1/4"	NT1616	5.6	2	1.660	1.660	2 1/8	2 3/8	1/2	5 1/8	3 1/2	2 1/8	3 1/8
1 1/2"	1/2"	NT1713	2.7	2	1.900	.840	2	2 3/8	3/8	5	2 1/8	2	3 1/8
1 1/2"	3/4"	NT1714	3.1	2	1.900	1.050	2	2 1/8	3/8	5 1/8	2 1/8	2	3 1/8
1 1/2"	1"	NT1715	3.3	2	1.900	1.315	2	2 1/8	3/8	5 1/8	2 1/8	2	3 1/8
1 1/2"	1 1/4"	NT1716	6.0	2	1.900	1.660	2 1/8	2 3/8	1/2	6 1/8	3 1/2	2 1/8	4 1/8
1 1/2"	1 1/2"	NT1717	6.5	2	1.900	1.900	2 1/8	2 3/8	1/2	6 1/8	3 1/2	2 1/8	4 1/8
2"	1/2"	NT1813	3.2	2	2.375	.840	2	3 1/8	3/8	5 3/8	2 1/8	2	3 3/8
2"	3/4"	NT1814	3.3	2	2.375	1.050	2	3 1/8	3/8	5 3/8	2 1/8	2	3 3/8
2"	1"	NT1815	3.7	2	2.375	1.315	2	3 1/8	3/8	5 3/8	2 1/8	2	3 3/8
2"	1 1/4"	NT1816	6.5	2	2.375	1.660	2 1/8	3 1/8	1/2	6 3/8	3 1/2	2 1/8	4 1/8
2"	1 1/2"	NT1817	7.2	2	2.375	1.900	2 1/8	3 1/8	1/2	6 3/8	3 1/2	2 1/8	4 1/8
2"	2"	NT1818	8.2	2	2.375	2.375	3 1/8	3 3/8	1/2	6 1/8	4 3/8	2 1/8	4 3/8
2 1/2"	1/2"	NT1913	3.4	2	2.875	.840	2	3 3/8	3/8	6 1/8	2 1/8	2	3 7/8
2 1/2"	3/4"	NT1914	3.8	2	2.875	1.050	2	3 1/8	3/8	6 1/8	2 1/8	2	3 7/8
2 1/2"	1"	NT1915	4.1	2	2.875	1.315	2	3 1/8	3/8	6 1/8	2 1/8	2	3 7/8
2 1/2"	1 1/4"	NT1916	6.9	2	2.875	1.660	2 1/8	3 1/8	1/2	7 1/8	3 1/2	2 1/8	4 5/8
2 1/2"	1 1/2"	NT1917	7.7	2	2.875	1.900	2 1/8	3 1/8	1/2	7 1/8	3 1/2	2 1/8	4 5/8
2 1/2"	2"	NT1918	9.2	2	2.875	2.375	3 1/8	3 3/8	1/2	7 1/8	4 3/8	2 1/8	4 5/8
2 1/2"	2 1/2"	NT1919	11	2	2.875	2.875	3 3/8	3 3/8	1/2	7 1/8	4 3/8	2 1/8	4 5/8
3"	1/2"	NT2013	4.3	2	3.500	.840	2	4 1/8	3/8	6 3/8	2 1/8	2	4 1/8
3"	3/4"	NT2014	4.4	2	3.500	1.050	2	4 1/8	3/8	6 3/8	2 1/8	2	4 1/8
3"	1"	NT2015	4.7	2	3.500	1.315	2	4 1/8	3/8	6 13/16	2 1/8	2	4 1/8
3"	1 1/4"	NT2016	7.8	2	3.500	1.660	2 1/8	4 1/8	1/2	7 3/8	3 1/2	2 1/8	4 1/8
3"	1 1/2"	NT2017	8.7	2	3.500	1.900	2 1/8	4 1/8	1/2	7 13/16	3 1/2	2 1/8	4 1/8
3"	2"	NT2018	10	2	3.500	2.375	3 1/8	4 1/8	1/2	7 13/16	4 3/8	2 1/8	4 1/8
3"	2 1/2"	NT2019	10	2	3.500	2.875	3 3/8	4 1/8	1/2	7 13/16	5 1/8	2 1/8	4 1/8
3"	3"	NT2020	17	2	3.500	3.500	4 3/8	4 3/8	5/8	8 3/8	6 3/8	3 1/4	5 1/8

(CONTINUED)

SHEET 1 OF 2 SHEETS
SUPERSEDES SC 11718-7

TEE CONNECTOR			
CAT. NO. NT			
DRAWN J.A.B. 5-3-48 CHECKED D.H. 10-16-57			
BURNEDY Corporation			
NORWALK, CONNECT.			
SA1171810			