



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	0		A	RELEASED PER EC 0512-0488-04	10JAN05	MY	SB
			A1	REVISED PER ECO-10-000445	11JAN10	KK	AEG



- 1 DRAWING AND DIMENSIONS SHOWN ARE FOR A SINGLE 278 I/O SOCKET ASSEMBLY.
- 2 THE POST DIAMETER REFERENCE DIMENSIONS EXCLUDE THE POSTS' FLUTING FEATURES.
- 3 CONTACT PADS SHALL BE PLATED WITH 0.0008 [0.0003] MINIMUM THICK GOLD OVER 0.0038 [0.0015] MINIMUM THICK NICKEL.
- 4 MATERIAL:
HOUSING- HIGH TEMPERATURE NYLON, BLACK.
EXTRACTORS- HIGH TEMPERATURE NYLON, NATURAL, BLACK.
CONTACTS- PHOSPHOR BRONZE WITH 0.00076[0.00030] MIN THICK GOLD OVER 0.0038[0.00150] MIN THICK NICKEL IN CONTACT AREA AND 0.0038[0.00150] MIN THICK MATTE TIN OVER 0.00127[0.00050] MIN THICK NICKEL ON SOLDER TAIL.
BOARDLOCKS, BRASS, AMP 100-86
- 5 5390108-4 DOES NOT HAVE CENTER POST.
- 6 BOARDLOCK DETAIL FOR 5390108-5 ONLY.
- 7 DATE CODE LOCATED APPROX. AS SHOWN.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	OBSOLETE	NATURAL	2.79[.110]	278	5390108-5
		BLACK	4.19[.165]	278	5390108-4 ⁵
		NATURAL	2.79[.110]	278	5390108-3
		EXTRACTOR	DIM_A	POS	PART NUMBER

TYPICAL DIMENSIONS TO CENTER LINE FOR THE CONTROLLING DIMENSIONING ORGANIZATION SHALL BE CONTACTED FOR THE LATEST EDITION.		DWN M. YEOMANS 10JAN05	tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK M. YEOMANS 10JAN05	NAME SOCKET ASSEMBLY, 16 BYTE DIMM, 1mm, 278 I/O	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BURKHOLDER 10JAN05	SIZE A100779C=5390108	
9 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	RESTRICTED TO -	
MATERIAL		SCALE 6:1	SHEET 1 OF 2	
4		REV A1		

