





Description: Straight BNC Crimp Plug For RG59, RG62 Style Cable
 Part No: CP782
 Application: For RG59, RG62 Cable
 Crimp Tool: 24-9859P
 Impedance: 75 Ohms
 Frequency Range: 0-2 GHz
 Material: Body: Brass Nickel plated
 Contact: Brass Gold plated
 Insulator: Teflon
 Crimp Sleeve: Brass Nickel plated
 Coupling Nut: Zinc Nickel plated
 RoHS Compliance: Yes
 Technical Detail: Refer to Emerson Document P/N 27-0000



DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	CHECKED BY	DATE
X	± 0.5	BETTY.YU	02-20-09
X.X	± 0.3	APPROVED BY	DATE
X.XX	± 0.1	THOMAS	02-20-09
ANGLES	$\pm 0.5^\circ$	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

DRAWING NO.	
CP782-CUST	
REVISIONS	
01	OFFICIAL RELEASE
02-20-09	I W B Y T
	Thomas Chow

CUSTOMER COPY



Connectivity
Solutions

TITLE
STRAIGHT BNC CRIMP PLUG
FOR RG59, RG62 STYLE CABLE

SHEET 1 OF 1 DRAWING NO. CP782-CUST SIZE A

受控 CONTROLLED DOCUMENT

编号 P/N	CP782-CUST	版本 Rev	01	日期 Rel'd Date	Apr29,09
--------	------------	--------	----	---------------	----------