

**Part Number: 79108-0005**

**2.00mm Pitch Milli-Grid™ Flex-to-Board Vertical Receptacle Dual Row Through-Hole, 0.38µm Gold (Au) Selective Plating, 12 Circuits, Tin/Lead**

Image not available

**Status:** **OBSOLETE**  
**Replacement:** [791081005](#)  
**Series:** [79108](#)  
**Category:** FFC/FPC Connectors  
**Overview:** [Milli-Grid™ Connector System](#)

Series image - Reference only

**Product Environmental Compliance**

**EU RoHS:** Not RoHS Compliant  
**China RoHS:**   
**REACH SVHC:** Contains SVHC: No  
**Low-Halogen Status:** Not Reviewed

**Part Detail****General**

|               |                                              |
|---------------|----------------------------------------------|
| <b>Status</b> | <b>Obsolete</b>                              |
| Category      | FFC/FPC Connectors                           |
| Series        | <a href="#">79108</a>                        |
| Obsolete Date | 2005/06/01                                   |
| Overview      | <a href="#">Milli-Grid™ Connector System</a> |
| Product Name  | Milli-Grid™                                  |

**Physical**

|                                |                 |
|--------------------------------|-----------------|
| Circuits (Loaded)              | 12              |
| Contact Position               | Top             |
| Durability (mating cycles max) | 50              |
| Entry Angle                    | 90° Angle       |
| Number of Rows                 | 2               |
| Orientation                    | Right Angle     |
| PC Tail Length                 | 1.27mm          |
| PCB Locator                    | No              |
| PCB Retention                  | None            |
| PCB Thickness - Recommended    | 0.60mm          |
| Packaging Type                 | Tube            |
| Pitch - Mating Interface       | 2.00mm          |
| Polarized to PCB               | No              |
| Stackable                      | No              |
| Surface Mount Compatible (SMC) | No              |
| Temperature Range - Operating  | -55°C to +105°C |
| Termination Interface: Style   | Through Hole    |
| Wire/Cable Type                | FFC/FPC         |

**Electrical****(Please review the Product Specification for specific details.)**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 1A   |
| Voltage - Maximum             | 125V |

**Solder Process Data**

|                                        |            |
|----------------------------------------|------------|
| Replacement RoHS Compliant Part Number | 0791081005 |
|----------------------------------------|------------|

**Material Info****Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application****Tooling**

[Check our list of old tooling that used to be available for this part](#)

