

PRODUCT NUMBER
73304-XXXLF

PLATING OPTION
1= GXT 0.76 μm
3= GOLD 0.76 μm
5= GOLD 1.27 μm


PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG

TERMINAL LOADING
1= FULLY LOADED
2= POS 1,2,7,8
3= POS 3,4,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.

NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.








CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MOD JACK			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
H		F06-0240		DLE		06.07.18		angles linear		±0.13			
J		F09-0070		LSA		02.07.23		mm 		SMT RA JACK			
K		B-15798		JFA		13.09.09		±2'		8 POS OUTSIDE			
L		F-21888		AMA		15.09.09		engr		D LEGRAND			
								F TISSERAND		03.01.27			
F		F04-0363		DLE		04.10.18		chr		JF NOTTEAU			
G		F05-0247		DLE		05.09.12		appd		F.TI			
										03.01.27			
sheet		revision		L		E		B		FCJ 			
index		sheet		1		2		3		dwg no			
										sheet 1 of 3			
										size			
										A3			
										73304			
										type			
										CUSTOMER Drawing			

PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3


CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code	surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family MOD-JACK
ltr	ecr no	dr	date	title SMT RA JACK 8 POS. OUTSIDE
D	D80620	DLE	98.11.26	
E	F06-024Q	DLE	06.07.18	
		angles	linear	scale 2:1
		dr	D LEGRAND 04.10.18	dwg no
		enrg	P NIZZI 04.10.18	73304
		chr	D LEGRAND 04.10.18	sheet 2 of 3
		appd	P NIZZI 04.10.18	A3
sheet index	revision sheet			type CUSTOMER Drawing



FCconnect.com

Copyright FCJ



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance	projection	product family	
				ISO 1302	ISO 406 ISO 1101		MOD JACK	
ltr	ecr no	dr	date	tolerances unless otherwise specified			title	
A	F04-0363	DLE	04.10.18	angles	±0.13			
B	F06-0240	DLE	06.07.18	linear		mm	SMT RA JACK 8 POS OUTSIDE	
				±2'		scale 2:1		
				dr	D LEGRAND 04.10.18		dwg no	
				engr	P NIZZI 04.10.18			
				chr	D LEGRAND 04.10.18		73304	
				appd	P.NZ 04.10.18			
sheet index		revision sheet					sheet 3 of - size	
							A4	
							type	
							CUSTOMER Drawing	

form: A4