




DO NOT  
SCALE FROM  
THIS PRINTFIG 1  
-01: THROUGH HOLE

SECTION "A"-A"

FIG 2  
-TR: TAPE & REEL OPTION

## NO OF POSITIONS


-05, -07, -10 THRU -50  
(PER ROW)

## LEAD STYLE

-01: THROUGH HOLE  
(SEE FIG 1)  
-02: SURFACE MOUNT  
(SEE FIG 3, SHT 2)

## PLATING SPECIFICATION

- S: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- L: 15μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- F: 3μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- H: 30μ" GOLD IN CONTACT AREA, 3μ" GOLD ON TAIL
- FM: 3μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- LM: 15μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- SM: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- STL: 30μ" SELECTIVE GOLD IN CONTACT AREA, TIN/LEAD (90/10+/-5%) TAIL



SECTION "B"-B"

TABLE 1	
NO OF POS.	"A"
EVEN	.310
ODD (EXCL. -05, -07 POS)	.360
-05, -07	.113

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS                    ANGLES  
.XX: ±.01                    2°  
.XXX: ±.005  
.XXXX: ±.0020

## MATERIAL:

VECTRA E130i, LCP, UL 94 VO  
COLOR: BLACK  
CONTACT: PHOS BRONZE, THICKNESS: .018

F:\DWG\MISC\MKTG\TFML-1XX-XX-XXX-D-XXX-MKT.SLDDRW

\* PROPRIETARY NOTE \*  
THIS DOCUMENT CONTAINS CONFIDENTIAL AND  
PROPRIETARY INFORMATION AND ALL DESIGN,  
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS  
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,  
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE  
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR  
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY  
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS  
WRITTEN CONSENT OF SAMTEC, INC.

## DO NOT SCALE DRAWING


SHEET SCALE: 1.75:1

## OPTION

- A: ALIGNMENT PIN (USE TFML-XX-D-01-A)  
(SEE FIG 7, SHT 3)
- LC: LOCKING CLIP (USE LC-05-TM) SEE NOTE 12  
(SEE FIG 9, SHT 3, N/A ON -RA OPTION)
- P: PICK & PLACE PAD (USE PPP-72 FOR -05 & -07)  
USE PPP-04 FOR -10 THRU -50)
- (AVAIL IN ALL POSITIONS, N/A  
ON -RA OPTION, SEE FIG 5, SHT 2)
- RA: RIGHT ANGLE (LEAD STYLE -01 ONLY)  
(SEE FIG 4, SHT 2)
- TR: TAPE & REEL  
(SEE FIG 2)(N/A ON -01 LEAD STYLE)
- SA: STAKED ALIGNMENT PIN (USE SM-A5)  
(SEE FIG 8, SHT 3)
- K: POLYAMIDE FILM (USE K-DOT-.217-313-005)  
(SEE FIG 6, SHT 2) (N/A ON -RA)
- SN: SOLDER NAIL (USE TFML-XX-D-01-SN &  
WT-27-01-T) (SEE FIG 10, SHEET 4)  
(AVAILABLE ON -02 LEAD STYLE ONLY)
- SN2: SOLDER NAIL FOR .093 BOARD  
(USE TFML-XX-D-01-SN &  
WT-27-02-T) (SEE FIG 10, SHEET 4)  
(AVAILABLE ON -02 LEAD STYLE ONLY)  
(NOT AVAILABLE WITH -A, -LC, -RA, -SA)

## ROW SPECIFICATION

- D: DOUBLE ROW



IN-PROCESS

## NOTES:

1.  $\odot$  REPRESENTS A CRITICAL DIMENSION.
2. COPLANARITY: POSITIONS -05 THRU -26: .004[0.10]  
POSITIONS -27 THRU -50: .006[0.15].
3. MANUFACTURING IN-PROCESS DIMENSION  $\odot$   
DESIGNED TO ACHIEVE FINISHED ASSEMBLY.
4. MINIMUM PUSHOUT FORCE: 12 OZ.  $\odot$
5. MAXIMUM ALLOWABLE BOW: .004 INCH/INCH  
[0.10 MM/MM]AFTER ASSEMBLY.
6. MEASURED FROM BEND.
7. POSITIONS -05 AND -07 WILL ONLY HAVE ONE CLIP AT  
DIMENSION SHOWN; POSITIONS -10 THROUGH -24  
WILL HAVE ONLY ONE CLIP AT DIMENSION SHOWN;  
POSITIONS -25 THROUGH -34 WILL HAVE TWO CLIPS AT  
DIMENSION SHOWN; POSITIONS -35 THROUGH -50 WILL  
HAVE THREE; CLIPS: TWO AT DIMENSION SHOWN & ONE  
CENTERED ON INSULATOR.
8. NOTE DELETED.
9. .003[0.08] MAXIMUM TERMINAL BURR
10. .005[0.13] MAXIMUM HEIGHT VARIATION BETWEEN ANY TWO PINS.
11. DIMENSION IS NOT APPLICABLE FOR -05 AND -07 POSITION.
12. DUE TO THE HIGH AMOUNT OF INSERTION FORCE  
NEEDED, THE -LC OPTION IS NOT COMPATIBLE  
WITH AUTO PLACEMENT. SAMTEC RECOMMENDS  
MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH  
THE -LC OPTION.

520 PARK EAST BLVD, NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047

e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:	.050 SHROUDED TERMINAL ASSEMBLY	
DWG. NO.	TFML-1XX-XX-XXX-D-XXX	
BY:	DEANP	4/8/99
SHEET 1 OF 4		

FIG 3

-02: SURFACE MOUNT  
(SHOWN: TFML-125-02-XXX-D)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)




FIG 4

-RA: RIGHT ANGLE OPTION  
(SHOWN: TFML-125-01-XXX-D-RA)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)





FIG 5

-P: PICK & PLACE PAD OPTION  
(SHOWN: TFML-125-02-XXX-D-P)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)  
NOTCH ON PAD TO BE ON SAME END AS NOTCH IN TFM BODY





FIG 6

-K: POLYIMIDE FILM PAD OPTION  
(SHOWN: TFML-125-02-XXX-D-K)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)




F:\DWG\MISC\MKTG\TFML-1XX-XX-XXX-D-XXX-MKT.SLDDRW


<p>PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</p> <p>DO NOT SCALE DRAWING</p> <p>SHEET SCALE: 1.75:1</p>	<p><b>Samtec</b> 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322</p> <p>DESCRIPTION: .050 SHROUDED TERMINAL ASSEMBLY</p> <p>DWG. NO. TFML-1XX-XX-XXX-D-XXX</p> <p>BY: DEANP 4/8/99 SHEET 2 OF 4</p>
--	--

PACKAGING VIEWS


PARTS TO BE POSITIONED WITH POLARIZING NOTCH FACING THE SAMTEC LOGO AND ARROW.



PARTS TO BE POSITIONED WITH TAILS FACING LOGO SIDE OF TUBE AND POLARIZING NOTCH ORIENTED AS SHOWN




POSITION PARTS WITH POLARIZING NOTCH ORIENTED AS SHOWN



LEAD STYLE	PACKAGING TUBE	PLUG
-RA ONLY	PT-1-24-05-17	TP-07
-01,-02 EXCEPT -RA OR -P	PT-1-24-01-09	TP-24
-01-P,-02-P	PT-1-24-03-09	TP-03


## FIG 7

-A: ALIGNMENT PIN OPTION  
(SHOWN: TFML-125-02-XXX-D-A)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)  
-NOT AVAILABLE WITH -RA




## FIG 8

-SA: STAKED ALIGNMENT PIN OPTION  
(SHOWN: TFML-125-02-XXX-D-SA)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)  
-NOT AVAILABLE ON -RA



## FIG 9

-LC: LOCKING CLIP OPTION  
(SHOWN: TFML-125-02-XXX-D-LC)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)  
-NOT AVAILABLE ON -RA





F:\DWG\MISC\MKTG\TFML-1XX-XX-XXX-D-XXX-MKT.SLDDRW

<p>* PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</p> <p>DO NOT SCALE DRAWING SHEET SCALE: 1.75:1</p>	<p><b>Samtec</b> 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322</p> <p>DESCRIPTION: .050 SHROUDED TERMINAL ASSEMBLY</p> <p>DWG. NO. TFML-1XX-XX-XXX-D-XXX</p> <p>BY: DEANP 4/8/99 SHEET 3 OF 4</p>
---	--

FIG 10

-SNX: SOLDER NAIL  
(SHOWN: TFXML-125-02-XXX-D-SN)  
(SAME AS FIG 1, UNLESS OTHERWISE STATED)  
(ONLY AVAILABLE ON -02 LEAD STYLE)



## SECTION "E"- "E"

TABLE 2	
OPTION	"B"
-SN	.071[1.80]
-SN2	.106[2.69]

**PROPRIETARY NOTE**  
\* THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOT REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3

**Samtec**

520 PARK EAST BLVD, NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail: [info@SAMTEC.com](mailto:info@SAMTEC.com) code: 55322

#### FIG. 10 SUBASSEMBLED TERMINAL ASSEMBLY

.05

WG. NO. TEMI-1XX-XX-XXXX-D-XXXX

TIME TAX XX

SHEET 4 OF 4