

## 7/16 DIN

7/16 DIN connectors are mechanically robust threaded coupling types designed for use with coaxial cables up to 17.3 mm dielectric diameter. Used in medium to high VHF and UHF fields. They are rated at 50 ohms and provide a low reflection factor up to 7.5 GHz. Various plating is available. All styles are currently built to order.

RoHS compliant

### N to 7/16

Part Number		Description	Fig. No.
131150011	<input checked="" type="checkbox"/>	N Male - 7/16 Female (TriPlate)	155A
153115011	<input checked="" type="checkbox"/>	N Male - 7/16 Male (TriPlate)	156A
153155011	<input checked="" type="checkbox"/>	N Female- 7/16 Male (TriPlate)	157A
153215011	<input checked="" type="checkbox"/>	N Female- 7/16 Female (TriPlate)	158A



Fig. 155A

Fig. 156A

Fig. 157A

Fig. 158

## 7/16 to 7/16

Part Number		Description	Fig. No.
1513A5011	<input checked="" type="checkbox"/>	7/16 Male - 7/16 Female R/A (Tri Plate)	155B
1532A5011	<input checked="" type="checkbox"/>	7/16 Female- 7/16 Female (TriPlate)	156B



Fig. 155B

Fig. 156B

## 7/16 to N Adapter Kit

**7/16 Adapter Kit ADPT3PA** is a 8 piece kit containing 7/16 to N, N to N and 7/16 to 7/16 adapters. Made of machined brass and Tri bodies. Gold plated contacts.

- Plated

Kits are in zippered leather cases.

Part Number		Description	Fig. No.
ADPT3PA	<input checked="" type="checkbox"/>	7/16 to NAdapter Kit (TriPlate)	155C



Fig. 155C

## Cable End or Panel Mount Styles

In some cases minimum order quantities will be required. These quantities will vary depending factors of tooling costs and total value. Contact Bon Interconnect sales office with your inquiry.



## GSK Style

This style connector is used in video, cellular and other applications where blind mating or PC board stacking is required. The beryllium grounding spring on the female excellent ground retention force. The contact mate is also rated for superior retention.

Available with 15 amp contacts

