



For more Information  
please call

1-800-Belden1



### Description:

22 AWG bare copper conductors, Flamarrest® insulation, conductors cabled, overall Beldfoil® tape shield (foil side out) and drain wire, Flamarrest® jacket with ripcord. Sequential footage marking every two feet.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	22	7	BC - Bare Copper

#### Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.229

#### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.381

Outer Jacket Ripcord: Yes

### Overall Cabling

Overall Cabling Color Code Chart:

Color
Black
Red
White
Green

Overall Nominal Diameter: 3.734 mm

### Mechanical Characteristics (Overall)

Operating Temperature Range:	0°C To +75°C
Bulk Cable Weight:	26.936 Kg/Km
Max. Recommended Pulling Tension:	186.824 N
Min. Bend Radius (Install)/Minor Axis:	38.100 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes

## 6502FE Multi-Conductor - Commercial Applications

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire &amp; Cable): Yes

MII Order #39 (China RoHS): Yes

## Flame Test

UL Flame Test: NFPA 262

CSA Flame Test: FT6

## Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 5502FE

## Electrical Characteristics (Overall)

## Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

108.273

## Nom. Capacitance Cond. to Other Conductor &amp; Shield:

Capacitance (pF/m)

193.579

## Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

53.1522

## Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

50.1993

## Max. Operating Voltage - UL:

Voltage

300 V RMS

## Max. Recommended Current:

Current

2.2 Amps per conductor @ 25°C

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6502FE 877U1000	305 MT	8.618 KG	NATURAL		4 #22 FLRST FS FLRST
6502FE 8771000	305 MT	8.618 KG	NATURAL	C	4 #22 FLRST FS FLRST
6502FE 877500	152 MT	4.309 KG	NATURAL		4 #22 FLRST FS FLRST

## Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 06-02-2008

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

## **6502FE Multi-Conductor - Commercial Applications**

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.  
Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.  
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.