

VC-M-KV-PG21(17-20,5)

Order No.: 1854051

The illustration shows a version of the product

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1854051>

Half screw connection Pg21, made of metal, consisting of rubber seal with one hole and one pressure screw, for type 2 - 4 housings, cable [mm] 17 - 20.5

Commercial data

GTIN (EAN)	
sales group	D290
Pack	5 pcs.
Customs tariff	74153300
Catalog page information	Page 373 (PC-2009)

Product notesWEEE/RoHS-compliant since:
03/27/2009

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Material, pressure screw	Nickel-plated brass
Seal material	TPE

Cable seal material	TPE
Wrench size, union nut	30 mm
Thread type on seal side	PG21
External cable diameter	17 mm ... 20.5 mm
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

Certificates / Approvals

Certification GOST

Accessories

Item	Designation	Description
------	-------------	-------------

Assembly

1854983	VC-M-KV-PG21- 0	Half screw connection made of metal with rubber seal without hole for sealing or for individual holes
---------	-----------------	---

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;