

## HDMI Extender Equalizer, Active Repeater for Video and Audio, 1920x1200,1080p at 60Hz (HDMI M/F) 1-ft.

MODEL NUMBER: **B123-001-60**



### Description

Tripp Lite's B123-001-60 HDMI Signal Extender increases the distance a 1080p @ 60Hz (or 1920 x 1200) signal can be transmitted beyond the recommended 16 ft. (5 m.). It supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 60Hz, at a maximum distance of 125 ft. from the source. Use P568-Series HDMI cables in most applications. When extending a 1080p @ 60Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100 ft. are available from Tripp Lite as a custom order) 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable. Simply connect the longer cable between the source and the B123-001-60, and the shorter cable (16 ft. or less) between the adapter and the monitor/TV. Software or drivers are not required. Built-in Equalization control to adjust the video image. HDCP compliant. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Features

- Extend a 1080p @ 60Hz (or 1920 x 1200) HDMI signal up to 125 ft. from the source
- Use P568-Series HDMI cables in most applications
- When extending a 1080p @ 60Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD.
- Lengths over 100 ft. are available from Tripp Lite as a custom order)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Built-in Equalization control to adjust the video image
- HDCP compliant
- No software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

### Highlights

- Extend a 1080p @ 60Hz (or 1920 x 1200) HDMI signal up to 125 ft. from the source
- When extending a 1080p @ 60Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- B123-001-60 HDMI Active Extender
- External Power Supply ( Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A )
- Screwdriver for Equalization adjustment



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

General Info	
Product Group	SPLITTERS, SWITCHES & EXTENDERS
OVERVIEW	
Cable Type	CAT5/CAT5E
Display Style	Signal Booster
Model Type	HDMI
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
CONNECTIONS	
Connector A	HDMI (MALE)
Connector B	HDMI (FEMALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.