





PLATING CODE&GOLD THICKNESS		E9 Au:1u		Z4 OR Z6 Au:0.8u		PART NUMBER		
						1AB000490028(LF)		
						BPS1B30D0CZ6(LF)		
						1AB000490026(LF)		
						BPS1B30D2CZ6(LF)		
						1AB000490012(LF)		
						BPS1B30D3CZ6(LF)		
5	HPTE1597	-	-	-	-	-	PLASTIC CABLE CLAMP	-
	HPTE1586	-	-	-	-	-	CABLE CLAMP #7.2	VAW19067
4	HPTE1585/A	-	-	-	-	-	CABLE CLAMP #12.5	VAW19066
	HPTE1585	-	-	-	-	-	CROSSHEEDED SCREW	VAW21269
		-	-	-	-	-	OR SLOTTED SCREW	VAW19065
3	BPBS1B30P7	-	-	-	1	-	1/2 CABLE HOOD FOR AWG30	VRW13124
	BPBS1B30P5	-	-	-	1	1	1/2 CABLE HOOD FOR AWG24 AWG26	
	BPBS1B30P6	-	-	-	1	-	1/2 CABLE HOOD FOR AWG30	VRW13125
	BPBS1B30P4	-	-	-	1	1	1/2 CABLE HOOD FOR AWG24 AWG26	
2	BPCD3P2---(LF)	-	-	-	-	30	CONTACT FOR AWG24(IDENTIFICATION-3)	
	BPCD2P2---(LF)	-	-	-	30	-	CONTACT FOR AWG26(IDENTIFICATION-2)	VTW10916
	BPCD0P2---(LF)	-	-	-	30	-	CONTACT FOR AWG30(IDENTIFICATION-0)	
1	BPBS1B30P9	-	-	-	1	-	BODY FOR AWG30(COLOR=WHITE)	
	BPBS1B30P8	-	-	-	1	-	BODY FOR AWG26(COLOR=BLACK)	VRW13121
	BPBS1B30P1	-	-	-	1	1	BODY FOR AWG24(COLOR=GREY)	
ITEM	CATALOG N°	QTY. FOR COMPLETE ASS'Y				DESCRIPTION		DRAWING

NOTES:
1.MATERIAL:
HOOD:THERMALPLATIC UL94V0;
BODY:GLASSFIBER REINFORCED THERMALPLASTIC UL94V0;
CONTACTS:PHOSPHOR BRONZE;
PLATING:GOLD OVER 2um NICKEL ON WORKING AREA.
2.MECHANICAL REQUIREMENT:
INSERTION FORCE(EACH CONTACT):<=1N;
WITHDRAWAL FORCE (EACH CONTACT):>=0.19N;
DURABILITY:>=100CYCLES.
3.ELECTRICAL REQUIREMENT:
INITIAL CONTACT RESISTANCE:<=20MILLIOHM;
INSULATION RESISTANCE AFTER TEST:>=10000MEGAOHM;
WITHSTANDING VOLTAGE:>1000Vrms;
OPERATING VOLTAGE:250VAC;
OPERATING CURRENT:1.3A AT 70 DEGREE.
4.IF LEAD FREE P/N, GS-14-920 SHOULD BE APPLIED.
5.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



mat'l. code				tolerances unless otherwise specified		INSPECTION COPY	A FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ± 0.3 .XX ± 0.13				
A	N05-0223	AILEI	09/05/05	linear		projection	title ASSY 2X15 CAPOT & CON. vxx27633		
				angles	±2°		product family DIN		code 213
				dr	LING GU 09/05/05	MM	size dwg no		sheet 1 of 1
				enr	AILEI ZHANG 09/05/05		A4 VJW54643		
				chr	AILEI ZHANG 09/05/05	scale 1:1			
				app	JASON ZHOU 09/05/05				
sheet index	revision sheet	A	1				cage code		