


1		2		3		4		5		6		7		8	
REVISIONS															
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE													



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

- 1. BRASS PER QQ-B-626
- 2. BRASS PER QQ-B-613
- 3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
- 4. SILVER PL. 200 MIN. THICK OVER COPPER STRIKE

8	CONTACT PIN	NOTE 1	NOTE 4	1	B2071B1-8	DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				PART NO. TM-FMEM-NDS-50		Amphenol TITLE FME MALE TO TNC MALE ADAPTOR DRAWING NO. KJ-TM-FMEM-NDS-50 ITEM NO.
7	WASHER	NOTE 2	NOTE 3	1	WS-12B/9X0B					APPROVED DATE 10-11-01'		
6	RING	DELFIN	NATURAL	1	T50000-6-A					CHECKED DATE 10-11-01'		
5	RETAINER RING	NOTE 1	NOTE 3	1	B50000-5					DRAWN DATE 10-11-01'		
4	GASKET	RUBBER	RED	1	GS-105/8X15							
3	INSULATOR	DELFIN	NATURAL	1	B50002-3-50							
2	BODY	NOTE 1	NOTE 3	1	B2071B1-2							
1	SHELL	NOTE 1	NOTE 3	1	T50000-1-B							
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	4/1	ISSUE	A	FILE NO.		