


ENERGIZER X22

9V




Industry Standard Dimensions



Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-1604A, IEC-6LR61
Nominal Voltage:	9.0 volts
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Typical Weight:	45.6 grams (1.6 oz.)
Typical Volume:	21.1 cubic centimeters (1.3 cubic inch)
Jacket:	Metal
Shelf Life:	5 years at 21°C (80% of initial capacity)
Terminal:	Miniature Snap

Milliamp-Hours Capacity

Continuous discharge to 4.8 volts at 21°C



Device Selection Guide:

Toy



Baby Monitor



Garage Opener




Clock Radio



Smoke Detector



Battery Selection Indicator



High Drain
Devices

Moderate
Drain
Devices

Low Drain
Devices

Important Notice


This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

ENERGIZER X22

9V


Constant Resistance Performance

Typical Characteristics (21°C)



Constant Current Performance


Typical Characteristics (21°C)



Industry Standard Tests (21°C)


RADIO

620 ohm 2 hrs/day




LIGHTING

270 ohm 1 hr/day



ACCELERATED SMOKE DETECTOR

10K/620 ohm 1 sec/hr pulse



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.