

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0460151800

Status:


Obsolete

Overview:

minifit_plus_hcs

Description:

4.20mm (.165") Pitch Mini-Fit® Plus HCS Header, Dual Row, Vertical, 18 Circuits, without Snap-in Plastic Peg PCB Lock, with Drain Holes, PA Polyamide Nylon 6/6, UL 94V-0, Tin (Sn) 1.27µm (50µ") Over Nickel (Ni) Plating



Documents:

[Drawing \(PDF\)](#)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	46015
Application	Power, Wire-to-Board
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit Plus® HCS Crimp Terminal Crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current de-rating information.
Overview	minifit_plus_hcs
Product Name	Mini-Fit® Plus HCS
Physical	
Breakaway	No
Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Natural
Durability (mating cycles max)	75
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	2
Orientation	Vertical
PC Tail Length	1.80mm (.071")
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.78mm (.070")
Packaging Type	Tray
Pitch - Mating Interface	4.20mm (.165")
Plating min - Mating	2.540µm (100µ")
Plating min - Termination	1.270µm (50µ")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No

EU RoHS

ELV and RoHS Compliant

REACH SVHC Not Reviewed

Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

46015Series

Mates With

5557 Mini-Fit Jr.™ Receptacle Housing

Temperature Range - Operating
Termination Interface: Style

-40°C to +105°C
Through Hole

Electrical

Current - Maximum per Contact
Voltage - Maximum

13A
600V

Material Info

This document was generated on 03/15/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION