

1 | 2 | 3 | 4 | 5 | 6


PRODUCT NUMBER  
95615-XXXXLF

PLATING  
0 = 0.20 $\mu$ m GOLD/GXT ON CONTACT AREA  
3.81 TIN LEAD ON TAIL  
1 = 0.76 $\mu$ m GOLD/GXT ON CONTACT AREA  
3.81 TIN LEAD ON TAIL  
3 = 0.38 $\mu$ m GOLD/GXT ON CONTACT AREA  
3.81 TIN LEAD ON TAIL  
5 = 0.38 $\mu$ m GXT FULL PLATED  
6 = 0.76 $\mu$ m GXT FULL PLATED  
7 = 0.76 $\mu$ m GOLD/GXT FULL PLATED  
9 = 0.20 $\mu$ m GOLD/GXT FULL PLATED



UNDERPLATING 1.27 $\mu$ m Ni MIN

WHEN "LF" IS REQUIRED, 2 $\mu$ m MATTE TIN OVER 1.27 $\mu$ m Ni MIN  
IS PROVIDED INSTEAD OF TIN LEAD, ONLY FOR PLATING 1, 3, 5

WHEN REQUIRED, ADD SUFFIX LETTER "LF"  
INDICATES THE PRODUCT IS RoHS  
COMPATIBLE, SEE NOTE 6 & 7  
PACKAGING, SEE NOTE 5  
TOTAL NB OF POSITIONS, 08 TO 34



STANDARD PICK-UP CAP



LARGE PICK-UP CAP NOTE 5  
NOT AVAILABLE FOR 2X2

NOTES:

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC  
UL 94V-0, COLOR CREAM

2. MATERIAL TERMINAL: COPPER ALLOY

3. TO DETERMINE DIMENSIONS:  
N = NUMBER OF POSITIONS PER ROW

4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.

5. PACKAGING:

= POLYBAGS

T = TUBE AVAILABILITY : FROM 2x5 UP TO 2x 17

B = TUBE WITH PICK UP CAP AVAILABLE FROM 2x5 UP TO 2x 17

K = TAPE AND REEL WITHOUT PICK-UP CAP, AVAILABLE FROM TA-845

A = TAPE AND REEL WITH LARGE PICK-UP CAP, NOT AVAILABLE FOR 2X2

TR = TAPE AND REEL WITH PICK-UP CAP, AVAILABLE FROM TA-845.

6. 95615-5XXXXF IS SIMILAR TO 95615-5XXX

95615-6XXXXF IS SIMILAR TO 95615-6XXX

THE SUFFIX "LF" IS ADDED FOR EASY LEAD FREE IDENTIFICATION

7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:




- "LF" MEANS THE PRODUCT IS LEAD-FREE,  
2 $\mu$ m MINIMUM MATTE TIN OVER 1.27 $\mu$ m  
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO  
260°C PEAK TEMPERATURE FOR 30 SECONDES  
MAX IN A CONVECTION, INFRA-RED OR VAPOR  
PHASE OR REFLOW OVEN.

c - LABELLING:

- MEETS PACKAGING SPECS AS PER GS-14-920  
d - THIS PRODUCT MEETS EUROPEAN DIRECTIVES  
AND OTHER COUNTRY REGULATIONS AS DISCRIBED  
IN GS-22-008.



mat'l. code SEE NOTES		surface ISO 1302		tolerance ISO 406 ISO		projection	product family MINITEK HEADER
lfr	ecn no	dr	date	tolerances unless otherwise specified			title
K	F05-0128	LMU	05.02.21	angles	.X ±0.3		SHR HEADER
L	F06-0210	LMU	06.07.05	linear	.XX ±0.13		2.00mm SMT
M	F07-0191	J.CO	07.09.05	±2°	.XXX ±0.05		
N	F08-0145	ELA	08.04.15	dr	JL.CORDIER	97.07.26	dwg no
P	F11-007	J.CO	11.06.17	engr	J.COMPAGNON	97.07.26	sheet 1 of 1
R	F11-0339	J.CO	11.12.06	chr	JL CORDIER	97.07.26	size
				appd	J COMPAGNON	97.07.26	A3
sheet	revision						
index	sheet						

