




T&B® Fittings

T&B Catalog Number:

LT450P

UPC Number:

78621045082

Description:

1/2" Non-Metallic liquidtight Bullet; -45; . For use with liquidtight non-metallic Type B conduit or liquidtight non-metallic tubing.

Status:

Active

Features

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.

Application

- The Bullet; meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.

General

- Trade Size (inches) 1/2
- Material Thermoplastic

Dimension Information

- Dimension A (inches) 0.570
- Dimension B (inches) 2.092
- Dimension C (inches) 1.448
- Dimension D-Minimum Throat (inches) 0.550
- E- NPT Thread (inches) 1/2-14
- Dimension F (inches) 1.590
- A (mm) 14.48
- B (mm) 53.14
- C (mm) 36.78
- D (mm) 13.97
- F Approx. (mm) 40.39

Specifications

- 3dmodel Available on Website

Packaging

- T&B Inner Pack 10
- Package in Units 50
- T&B Sold in UOM Each
- T&B Weight Per UOM 11.1 lbs. per 100

Application Support

- T&B Instruction Sheets ta00998-tb2
- Guide to Nonmetallic Conduit Applications Available on Website
- XTRAFLEX System Specifications Available on Website

Notes

-*Note

Suitable for hazardous locations; Class I Div 2;
Class II Div 1 & 2; Groups E, F, G; Class III per
N.E.C.; Article 501-4, 502-4 and 503-3

Certifications

-RoHS Compliance

Yes

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com